




P/N: 2-2330550-1 AS SHOWN



NOTES:




1. MATERIAL:
 - ① P4 TFLM BOLSTER PLATE: STAINLESS STEEL
 - ② P4 TFLM BOLSTER INSULATOR: POLYCARBONATE FILM PLUS ACRYLIC ADHESIVE LAYER
 - ③ ICX TFLM SPRING-1: MUSIC WIRE, NICKEL PLATING
 - ④ ICX TFLM SPRING-2: MUSIC WIRE, NICKEL PLATING
 - ⑤ ICX TFLM SPRING STUD: STAINLESS STEEL
 - ⑥ ICX TFLM M3 NUT: CARBON STEEL, NICKEL PLATING
 - ⑦ ICX TFLM NUT CAP-SIDE: THERMO-PLASTIC, UL94V-0, BLACK
 - ⑧ ICX TFLM NUT CAP: THERMO-PLASTIC, UL94V-0, BLACK
 - ⑨ ICX TFLM WIRE STOP PIN: STAINLESS STEEL
2. ASSEMBLED WITH BACKPLATE ASSEMBLY P/N: 2330551 SERIES
3. INDICATED DATE CODE ON THE BOLSTER PLATE



6	ICX TFLM WIRE STOP PIN	9
4	ICX TFLM NUT CAP, BLACK	8
2	ICX TFLM NUT CAP, SIDE, BLACK	7
6	ICX TFLM M3 NUT	6
4	ICX TFLM SPRING STUD	5
2	ICX TFLM SPRING-2	4
2	ICX TFLM SPRING-1	3
1	P4 TFLM BOLSTER INSULATOR	2
1	P4 TFLM BOLSTER PLATE	1
Q'TY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JEFF WANG 08FEB2018	TE Connectivity	
DIMENSIONS: mm		CHK: BILL LV 08FEB2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVO: SIMON LI 08FEB2018		
MATERIAL: -		PRODUCT SPEC: -		
APPLICATION SPEC: -		SIZE: A200779	DRAWING NO: C-2330550	
WEIGHT: -		RESTRICTED TO: -		
CUSTOMER DRAWING		SCALE: 1:1		SHEET: 1 OF 5

P/N: 2-2330550-2 AS SHOW



NOTES:




- MATERIAL:
 - P4 TFLM BOLSTER PLATE: STAINLESS STEEL
 - P4 TFLM BOLSTER INSULATOR: POLYCARBONATE FILM PLUS ACRYLIC ADHESIVE LAYER
 - ICX TFLM SPRING-1: MUSIC WIRE, NICKEL PLATING
 - ICX TFLM SPRING-2: MUSIC WIRE, NICKEL PLATING
 - ICX TFLM SPRING STUD: STAINLESS STEEL
 - ICX TFLM M3 NUT : CARBON STEEL, NICKEL PLATING
 - ICX TFLM NUT CAP-SIDE: THERMO-PLASTIC, UL94V-0, BLACK
 - ICX TFLM NUT CAP: THERMO-PLASTIC, UL94V-0, BLACK
 - ICX TFLM WIRE STOP PIN: STAINLESS STEEL
 - DUST COVER: PC+ABS, UL94V-0, GREY
- ASSEMBLED WITH BACKPLATE ASSEMBLY P/N: 2330551 SERIES
- BOLSTER ASSY WITH DUST COVER, ALL DIMENSIONS ARE THE SAME AS PN 2-2330550-1.

REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-

1	DUST COVER, GREY	10
6	ICX TFLM WIRE STOP PIN	9
4	ICX TFLM NUT CAP, BLACK	8
2	ICX TFLM NUT CAP, SIDE, BLACK	7
6	ICX TFLM M3 NUT	6
4	ICX TFLM SPRING STUD	5
2	ICX TFLM SPRING-2	4
2	ICX TFLM SPRING-1	3
1	P4 TFLM BOLSTER INSULATOR	2
1	P4 TFLM BOLSTER PLATE	1
Q'TY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: 08FEB2018 JEFF WANG	 TE Connectivity	
DIMENSIONS: mm		CHK: 08FEB2018 BILL LV		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: 08FEB2018 SIMON LI		
	0 PLC	±0.3	SOCKET P4 TFLM ASSY WITH DUST COVER	
	1 PLC	±0.3		
	2 PLC	±0.3		
	3 PLC	±0.3		
	4 PLC	±0.3		
ANGLES		±0.3	SIZE CAGE CODE DRAWING NO A200779C-2330550	
FINISH				
MATERIAL			RESTRICTED TO	
-	-	-	-	
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 5
			REV B1	

P/N: 3-2330550-1 AS SHOW



NOTES:




1. MATERIAL:
 - ① P5 TFLM BOLSTER PLATE: STAINLESS STEEL
 - ② P5 TFLM BOLSTER INSULATOR: -POLYCARBONATE FILM PLUS ACRYLIC ADHESIVE LAYER
 - ③ ICX TFLM SPRING-1: MUSIC WIRE, NICKEL PLATING
 - ④ ICX TFLM SPRING-2: MUSIC WIRE, NICKEL PLATING
 - ⑤ ICX TFLM SPRING STUD: STAINLESS STEEL
 - ⑥ ICX TFLM M3 NUT : CARBON STEEL, NICKEL PLATING
 - ⑦ ICX TFLM NUT CAP-SIDE: THERMO-PLASTIC, UL94V-0, GREY
 - ⑧ ICX TFLM NUT CAP: THERMO-PLASTIC, UL94V-0, GREY
 - ⑨ ICX TFLM WIRE STOP PIN: STAINLESS STEEL
2. ASSEMBLED WITH BACKPLATE ASSEMBLY P/N: 2330551 SERIES
3. INDICATED DATE CODE ON THE BOLSTER PLATE

6	ICX TFLM WIRE STOP PIN	9
4	ICX TFLM NUT CAP, GREY	8
2	ICX TFLM NUT CAP, SIDE, GREY	7
6	ICX TFLM M3 NUT	6
4	ICX TFLM SPRING STUD	5
2	ICX TFLM SPRING-2	4
2	ICX TFLM SPRING-1	3
1	P5 TFLM BOLSTER INSULATOR	2
1	P5 TFLM BOLSTER PLATE	1
Q'TY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN	08FEB2018	JEFF WANG	
		CHK	08FEB2018	BILL LV	
		APVO	08FEB2018	SIMON LI	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:			
mm		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT			
		CUSTOMER DRAWING			
		SCALE 1:1 SHEET 3 OF 5 REV B1			
MATERIAL		NAME			
-		SOCKET P5 TFLM ASSY WITHOUT DUST COVER			
-		SIZE CAGE CODE DRAWING NO			
-		A200779 C=2330550			
-		RESTRICTED TO			
-		-			

REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-

P/N: 3-2330550-2 AS SHOW





NOTES:

- MATERIAL:
 - P5 TFLM BOLSTER PLATE: STAINLESS STEEL
 - P5 TFLM BOLSTER INSULATOR: -POLYCARBONATE FILM PLUS ACRYLIC ADHESIVE LAYER
 - ICX TFLM SPRING-1: MUSIC WIRE, NICKEL PLATING
 - ICX TFLM SPRING-2: MUSIC WIRE, NICKEL PLATING
 - ICX TFLM SPRING STUD: STAINLESS STEEL
 - ICX TFLM M3 NUT : CARBON STEEL, NICKEL PLATING
 - ICX TFLM NUT CAP-SIDE: THERMO-PLASTIC, UL94V-0, GREY
 - ICX TFLM NUT CAP: THERMO-PLASTIC, UL94V-0, GREY
 - ICX TFLM WIRE STOP PIN: STAINLESS STEEL
 - DUST COVER: PC+ABS, UL94V-0, GREY
- ASSEMBLED WITH BACKPLATE ASSEMBLY P/N: 2330551 SERIES
- BOLSTER ASSY WITH DUST COVER, ALL DIMENSIONS ARE THE SAME AS PN 3-2330550-1.

1	DUST COVER, GREY	10
6	ICX TFLM WIRE STOP PIN	9
4	ICX TFLM NUT CAP, GREY	8
2	ICX TFLM NUT CAP, SIDE, GREY	7
6	ICX TFLM M3 NUT	6
4	ICX TFLM SPRING STUD	5
2	ICX TFLM SPRING-2	4
2	ICX TFLM SPRING-1	3
1	P5 TFLM BOLSTER INSULATOR	2
1	P5 TFLM BOLSTER PLATE	1
Q'TY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN JEFF WANG 08FEB2018	TE Connectivity	
DIMENSIONS mm		CHK BILL LV 08FEB2018	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVO SIMON LI 08FEB2018	PRODUCT SPEC	
MATERIAL		APPLICATION SPEC		RESTRICTED TO
FINISH		WEIGHT		SIZE CAGE CODE DRAWING NO
CUSTOMER DRAWING		A200779		C=2330550
SCALE 1:1		SHEET 4 OF 5		REV B1

REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-



KOZ LEGEND	
	ZONE 1: BOLSTER PLATE ZONE, NO OTHER COMPONENT PLACEMENT ALLOWED, 0.0MM HEIGHT RESTRICTION
	ZONE 2: SOCKET CAVITY 1.222 MM MAX HEIGHT RESTRICTION
	ZONE 3: SOCKET CAVITY TO SOCKET ZONE NO OTHER COMPONENT PLACEMENT ALLOWED, 0.0MM HEIGHT RESTRICTION
	ZONE 4: NO ROUTE ZONE, THROUGH ALL LAYERS
	ZONE 5: PRIMARY SIDE COMPONENT PLACEMENT ZONE MAX. COMPONENT HEIGHT OF 1.5MM

REFERENCE BOLSTER KEEPOUT ZONE

FOR GENERAL BOARD DESIGN, PLEASE REFER TO THE THERMAL AND MECHANICAL DESIGN GUIDELINES PROVIDED BY INTEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JEFF WANG 08FEB2018	TE Connectivity	
DIMENSIONS: mm		CHK: BILL LV 08FEB2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: SIMON LI 08FEB2018	NAME: SOCKET P4/P5 TFLM KOZ	
0 PLC ±0.3		PRODUCT SPEC	SIZE: CAGE CODE: DRAWING NO: A200779 ©=2330550	
1 PLC ±0.3		APPLICATION SPEC	RESTRICTED TO	
2 PLC ±0.3		WEIGHT	SCALE: 3:2 SHEET: 5 OF 5 REV: B1	
3 PLC ±0.3		CUSTOMER DRAWING		
4 PLC ±0.3				
ANGLES ±0.3				
FINISH				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2330550-2](#)