

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	N/A ,N/A .
(C) COPYRIGHT N/A BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		


LOC	DIST	REVISIONS					
DF	X0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER 0G3D-0423-02	8-02	JMK	JL

COMPONENT	MATERIAL	FINISH
HOUSING CLAMP NUT COUPLING NUT	STAINLESS STEEL PER ASTM-A-484 OR ASTM-A-582 TYPE 303	PASSIVATED PER ASTM-A-380 —
— DIELECTRIC —	PTFE FLUORCARBON PER ASTM-D-1457 —	— — —
— CENTER CONTACT —	BRASS PER ASTM-B-16 HALF HARD —	GOLD PLATED PER ASTM-B-488 —
— INNER SLEEVE	STAINLESS STEEL PER ASTM-A-484 OR ASTM-A-582 TYPE 303	GOLD PLATED PER ASTM-B-488 —
— GASKET —	SILICONE RUBBER PER ZZ-R-765 —	— — —
— FERRULE —	COPPER OR BRASS ALLOY, ROCKWELL F65 MAX	GOLD PLATED PER ASTM-B-488 —
— RETAINING RING —	BERYLLIUM COPPER PER ASTM-B-194 ALLOY C17200, CONDITION H	— — —
— — —	— — —	— — —


ENVIRONMENTAL
TEMPERATURE RATING: -65°C TO +165°C
VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
SHOCK: MIL-STD-202, METHOD 213, CONDITION 1
MOISTURE RESISTANCE: MIL-STD-202, METHOD 106
CORROSION: MIL-STD-202, METHOD 101, CONDITION B. 5% SALT SPRAY
THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B EXCEPT HIGH TEMP 85°C

MECHANICAL		
INTERFACE DIMENSIONS: MIL-STD-348A FIG.	310.1	
RECOMMENDED MATING TORQUE: 7-10 IN-LBS		
FORCE TO ENGAGE & DISENGAGE (IN-LBS MAX:)	2.0	
WEIGHT (GRAMS):	TBD	
MATING CHARACTERISTICS:	INSERTION (MAX LBS)	N/A
	WITHDRAWAL (MIN OZ):	N/A
CABLE RETENTION:	AXIAL FORCE (LBS)	10 MIN
	TORQUE (IN-OZ):	N/A
CENTER CONTACT CAPTIVATION:	AXIAL (LBS):	6.0
	RADIAL (IN-OZ):	N/A

ELECTRICAL	
NORMAL IMPEDANCE (OHMS):	50
FREQUENCY RANGE (GHz):	DC TO 12.4
VOLT RATING @ SEA LEVEL (VRMS MAX):	170
VSWR:	1.20+.025f(GHz)
INSERTION LOSS: (dB MAX):	.06 $\sqrt{f(\text{GHz})}$
RF LEAKAGE (dB MIN):	-60 @ 2-3 GHz
CORONA 70,000 FT (VRMS MIN):	125
DIELECTRIC WITHSTANDING VOLTAGE (VRMS MIN) AT SEA LEVEL:	500
I.R. (MEGOHMS MIN):	5,000
RF HIGH POTENTIAL AT SEA LEVEL (VRMS MIN @ 5 MHz):	335
CONTACT RESISTANCE (MILLIOHMS MAX):	
	CENTER CONTACT: 3.0
	OUTER CONTACT: 2.0
	CABLE TO HOUSING: 0.5




AS SHIPPED TO CUSTOMER



ASSEMBLED VIEW

1 $\varnothing$. 018 [0. 46] LOCKWIRE HOLE, 3 PLACES EQUALLY SPACED.

DESIGNED TO USE RG-178/U OR EQUIVALENT	
CABLE ENTRY DIAMETER MIN	
HOUSING:	N/A
CONTACT:	.021 [0.53]
DIELECTRIC:	.021 [0.53]
SLEEVE:	.036 [0.91]
FERRULE:	.098 [2.49]

THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES [mm]		
		
		0 PLC ± -
		1 PLC ± -
		2 PLC ± -
		3 PLC ± .005 [0.13]
		4 PLC ± -
		ANGLES ± -
MATERIAL	FINISH	
SEE TABLE	SEE TABLE	

DWN 8-27-02		 Tyco Electronics Corporation Harrisburg, PA 17105	
J. KAISER			
CHK 10-9-02	J. LIPPETT	NAME SMA STRAIGHT CABLE PLUG SOLDER CLAMP ATTACHMENT (M39012/55-3006) CAT A	
APVD 10-9-02	J. LIPPETT		
PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-1051757 —	
—			
APPLICATION SPEC			
408-4904		CUSTOMER DRAWING	
WEIGHT TBD		SCALE 1:1 SHEET 1 OF 1 REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1051757-1](#)