


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED/REDRAWN PER E.O. P17001	08DEC2000	SP	RDR
	D	REVISED PER E.O. P19555	11JUL2007	JA	RDR
	E	REVISED PER E.O. P20396	25JUN2010	JA	RDR
	F	REVISED PER ECO-15-007761	28MAY2015	RL	DM



- 3 MATERIAL:
BODY: .012 [0.30] THICK COPPER ALLOY
SLEEVE: STAINLESS STEEL
2. WIRE RANGE: 18 AWG TO 14 AWG [0.75-2.0 mm²]
INSULATION RANGE: $\varnothing .075 - .140$ [$\varnothing 1.91 - 3.56$]
- 1 APPLIES ONLY TO SELECTIVE GOLD 1062-16-0744.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	01DEC2000
		CHK	STEVE PALLUTH
		CHK	ALEX ROLINSKI
		APVD	R. REED
		APVD	08DEC2000
DIMENSIONS: INCHES[mm]		PRODUCT SPEC	0425-015-0000
		APPLICATION SPEC	114-151000
		WEIGHT	0.43 g
MATERIAL		FINISH	SEE TABLE
		Customer Drawing	

TE INTERNAL PN		DEUTSCH PN	PLATING
1062-16-0722		1062-16-0722	NICKEL
1062-16-0744		1062-16-0744	SELECTIVE GOLD
1062-16-0777		1062-16-0777	TIN
TE TE Connectivity			
NAME SOCKET, STAMPED AND FORMED SIZE 16 14-18AWG			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C=1062-16-07XX	-
SCALE 6:1		SHEET 1 OF 1	REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1062-16-0722 \(Mouser Reel\)](#) [1062-16-0722 \(Cut Strip\)](#) [1062-16-0722 \(Loose Piece\)](#)