

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		E2	REVISED PER ECO-11-004820	11MAR11	RK	HMR

AMP WIRE RANGE	 Listed FILE E13288
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	N/A

- 1

STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16
- 2

0.00254 [.000100] MIN TIN PER ASTM B-545
- 3


GOLD PLATE 0.00127 [.000050] MIN THK PER
MIL-G-45204 OVER NICKEL PLATE 0.00076
[.000030] MIN THK PER QQ-N-290
- 4

CLEANED, UNPLATED
- 5

COPPER PER ASTM B-152, ANNEALED

100	LOOSE PIECE, BOX	2	8-34107-1
5000	ON TAPE	2	2-34107-2
-	LOOSE PIECE	4	34107-2
-	LOOSE PIECE	3	34107-1
-	LOOSE PIECE	2	34107
QTY	PACKAGE TYPE	FINISH	PART NO.

CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-10-93	 TE Connectivity						
DIMENSIONS: MM [INCHES]		CHK DA PATTERSON 3-10-93							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME						
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		TERMINAL, RING TONGUE, SOLISTRAND -						
	FINISH		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL	- 	SEE TABLE	A2		00779	C-34107	-		
CUSTOMER DRAWING			SCALE		10:1	SHEET	1 of 1	REV	E2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34107](#)