






- 1 KEY HOLE ORIENTATION (DIM A) PER MATING GUIDE MODULE PART NUMBER TABLE (ORIENTATION SHOWN ON PCB LAYOUT IS FOR 1-1410353-2).
- 2 ANNULAR RING PLATED AROUND GUIDE PIN MOUNTING HOLE ON TOP AND BOTTOM SIDE OF BOARD.
- 3 FINISH:
3.81µm MINIMUM SILVER IN CONTACT AREA
OVER NICKEL OVER COPPER ALL OVER.
- 4 MATERIAL: ZINC ALLOY.



3	5.70	1-1410355-4
3	4.20	1-1410355-3
3	2.60	1-1410355-2
FINISH	DIM "G"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

B. CARBO

04AUG2011

CHK

A. SHARPE

04AUG2011

APVD

A. SHARPE

04AUG2011

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.5

2 PLC ±0.13

3 PLC ±0.013

4 PLC ±

ANGLES ±

FINISH

MATERIAL

4 -

PRODUCT SPEC

108-2072

APPLICATION SPEC

114-13056

WEIGHT

-

CUSTOMER DRAWING

NAME

KEYED GUIDE PIN, DIE CAST BACKPLANE CONNECTOR, MULTIGIG, THREADED POST

SIZE

A2

CAGE CODE

00779

DRAWING NO

1410355

RESTRICTED TO

-

SCALE

5:1

SHEET

1


OF

2


REV

A

LOC	DIST	REVISIONS				
CG	00	P	LTR	DESCRIPTION	DATE	APVD
		-		SEE SHEET 1	-	-



ALTERNATE PCB LAYOUT
FOR GUIDE POST
SCALE 4:1



TIER 2
GUIDE PIN FOOTPRINT
(20.3mm SIGNAL MODULES)
SCALE 4:1

3	-	1-1410353-9
3	315°	1-1410353-8
3	270°	1-1410353-7
3	90°	1-1410353-3
3	45°	1-1410353-2
3	0°	1-1410353-1
FINISH	DIM "A"	20.3mm GUIDE MODULE
	MATING GUIDE MODULE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO 04AUG2011	TE Connectivity		
DIMENSIONS: mm		CHK A. SHARPE 04AUG2011			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE 04AUG2011	NAME KEYED GUIDE PIN, DIE CAST BACKPLANE CONNECTOR, MULTIGIG, THREADED POST		
0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-2072 APPLICATION SPEC 114-13056 WEIGHT -			
MATERIAL		CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779	DRAWING NO 1410355
			SCALE 1:1	SHEET 2	OF 2
				REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1410355-2](#)