






P	LTR	DESCRIPTION	DATE	DWN	APVD
	CI	REVISED FOR ET00-0015-02	07 FEB 02	M.P.	R.M.

SCALA 1:1
(SCALE)SEZIONE B-B
(SECTION)

SECTION A-A





1) QUESTO PARTICOLARE VA USATO CON IL DISPOSITIVO DI AGGANCIO SECONDARIO TYCO P/N 282706-1
(THIS PART MUST BE USED WITH DOUBLE LOCK PLATE TYCO P/N 282706-1)

2) PER IL DISEGNO DELLA CONTROPARTE VEDI FOGLIO 2 DI 2
(FOR COUNTERPART DETAIL SEE SHEET 2 OF 2)

3 C.P.A. IN POSIZIONE PRE-ASSEMBLATA
(C.P.A. PRE-ASSEMBLED POSITION)

4 C.P.A. IN POSIZIONE CHIUSA, QUANDO IL CONNETTORE E' CORRETTAMENTE ACCOPPIATO CON LA CONTROPARTE
(C.P.A. IN CLOSED POSITION, WHEN THE CONNECTOR IS PROPERLY MATED WITH THE COUNTERPART)

GIALLO (YELLOW)	PA 6.6 CAR. VETRO (PA 6.6 GF)	C.P.A.	3	282703-1
GIALLO (YELLOW)	GOMMA SILICONICA (SILICONE RUBBER)	GUARNIZIONE (SEAL RING)	2	
NERO (BLACK)	PBT NATURALE (PBT UNFILLED)	BLOCCHETTO (HOUSING)	1	
COLORE (COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)	COMPONENTE No (ITEM No)	NUMERO (PART NUMBER)


SCALA 1:1
(SCALE)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±0.3
1 PLC	±0.3
2 PLC	±0.3
3 PLC	±
4 PLC	±
ANGLES	±2°
MATERIAL	FINISH
VEDERE TABELLA (SEE TABLE)	---

DWN	12SEP1995
CHK	12SEP1995
APVD	-
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	-

tyco Electronics		tyco Electronics AMP Italia S.p.A. C.so F.lli Cervi, 15 - Collegno (TO)	
NAME 3 POS. ECONOSEAL J-MK11+ CONN. PLUG ASS'Y			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=282703	-
SCALE 2:1		SHEET 1 OF 2	REV CI



SCALA 2:1 (SCALE)

SECTION A-A

DETTAGLIO J
SCALA 10:1
(DETAIL J - SCALE 10:1)

SEE DETAIL W

DATUM LINE

DETTAGLIO W
SCALA 5:1
(DETAIL W - SCALE 5:1)

1 QUOTE VALIDE SU TUTTO IL CONTOURNO
(THESE DIMENSIONS ARE VALID ALL AROUND)

2 TRATTO PRIVO DI BAVE E SEGNI DI
GIUNZIONE SU TUTTO IL CONTOURNO
(ZONE WITH NO FLASH AND WELDING
LINES ALL AROUND)

DETTAGLI CONTROPARTE HEADER
(TAB HEADER COUNTERPART DETAILS)

STAGNATO 2-4 micron (TINNED 2-4 micron)	OTTONE - HALF HARD (BRASS - HALF HARD)	CONTATTO (TAB)	2
---	PA 6.6 UNFILLED OR 15% G.F.	BLOCCHETTO (HOUSING)	1
FINITURA (FINISH)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)	ITEM No.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0.3 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±2°
MATERIAL VEDERE TABELLA (SEE TABLE)	FINISH VEDERE TABELLA (SEE TABLE)

DWN A. BAJ 12SEP1995	CHK C. TARTARI 12SEP1995
APVD -	PRODUCT SPEC -
APPLICATION SPEC -	WEIGHT -
CUSTOMER DRAWING	

tyco Electronics AMP Italia S.p.A. C.so F.lli Cervi, 15 - Collegno (TO)			
NAME 3 POS. ECONOSEAL J-MK11+ CONN. PLUG ASS'Y			
SIZE A3	CAGE CODE 00779	DRAWING NO C-282703	RESTRICTED TO -
SCALE 2:1		SHEET 2 OF 2	REV C1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[282703-1](#)