


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	REVISED PER ECN-22-150900	27APR2022	RK	CSD

AMP

WIRE RANGE

6 AWG
STRANDED



- 1 BODY MATERIAL THK 1.143±0.051[.045±.002]
- 2 FOR 7.975[0.314] MAX WIRE INS.
- 3 STAMP AMP 6* 23-30 APPROX AS SHOWN.

100	LOOSE PC	324049
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 6-18-93		 TE Connectivity														
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 6 AWG -											
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 10.5-16.8mm ² [20,800-33,100] STRANDED		MATERIAL BODY: COPPER PER ASTM B-152 INSULATION: NYLON ASTM D4066 TYPE I		FINISH BODY: TIN PLATE PER ASTM B545 INSULATION: COLOR-BLUE		APVD B. BARE 6-18-93						PRODUCT SPEC -		APPLICATION SPEC -		SIZE A3		CAGE CODE 00779	
FOR ORDER ENTRY			1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.								CUSTOMER DRAWING				SCALE NTS		SHEET 1 OF 1		REV G3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[324049](#)