



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-19-009164	24JUN2020	KG	DR



- 1 WIRE RANGE IS FOR 2 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 52,600-83,700 CMA, STRANDED WIRE.
- 2 TERMINAL BODY MATERIAL THK IS 1.778±0.076[.070±.003].
- 3 RECOMMENDED OPERATING TEMP -55°C [131°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
- 4 HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL
- 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162.

1	1-1196717-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 15.88[.625]MIN ID X 38.10±2.03[1.50±.08] RT555-5/8-0-SP
1	2-322870-2	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 08DEC09	TE Connectivity					
		CHK TOM MICHIELUTTI 08DEC09						
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHIELUTTI 08DEC09	NAME —					
	0 PLC ± —	PRODUCT SPEC — 	HEAT RESISTANT TERMINAL KIT WIRE SIZE: 2 AWG				RESTRICTED TO —	
	1 PLC ± —	— 						
	2 PLC ± —							
	3 PLC ± 0.127 [.005]	APPLICATION SPEC — 	SIZE A3	CAGE CODE 00779	DRAWING NO C-696643			
	4 PLC ± —	WEIGHT —						
	ANGLES ± 1°							
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[696643-1](#)