



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECR-16-011494	20JUN2017	NK	CX






















2 PLATING: CONTACTS - 2.54μm MINIMUM TIN-LEAD OVER 1.27μm MINIMUM NICKEL.
HOLDDOWNS: 2.54μm MINIMUM TIN-LEAD OVER 1.27μm MINIMUM NICKEL.

5 KAPTON VACUUM PICK UP BUTTON.

6 PLATING: CONTACTS - 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM NICKEL.
HOLDDOWNS: 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM NICKEL.



		33.00	40.41	40.00	12	3-1445053-2
		30.00	37.41	37.00	11	3-1445053-1
		27.00	34.41	34.00	10	3-1445053-0
		24.00	31.41	31.00	9	2-1445053-9
		21.00	28.41	28.00	8	2-1445053-8
		18.00	25.41	25.00	7	2-1445053-7
		15.00	22.41	22.00	6	2-1445053-6
		12.00	19.41	19.00	5	2-1445053-5
		9.00	16.41	16.00	4	2-1445053-4
		6.00	13.41	13.00	3	2-1445053-3
		3.00	10.41	10.00	2	2-1445053-2
	SUPERSEDED BY 3-1445053-2		33.00	40.41	40.00	12
SUPERSEDED BY 3-1445053-1		30.00	37.41	37.00	11	3-1445053-1
SUPERSEDED BY 3-1445053-0		27.00	34.41	34.00	10	3-1445053-0
SUPERSEDED BY 2-1445053-9		24.00	31.41	31.00	9	2-1445053-9
SUPERSEDED BY 2-1445053-8		21.00	28.41	28.00	8	2-1445053-8
SUPERSEDED BY 2-1445053-7		18.00	25.41	25.00	7	2-1445053-7
SUPERSEDED BY 2-1445053-6		15.00	22.41	22.00	6	2-1445053-6
SUPERSEDED BY 2-1445053-5		12.00	19.41	19.00	5	2-1445053-5
SUPERSEDED BY 2-1445053-4		9.00	16.41	16.00	4	2-1445053-4
SUPERSEDED BY 2-1445053-3		6.00	13.41	13.00	3	2-1445053-3
SUPERSEDED BY 2-1445053-2		3.00	10.41	10.00	2	2-1445053-2
	FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 07OCT2000		TE Connectivity	
DIMENSIONS: mm		CHG K. WHITAKER 20-FEB-2001		 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 20-FEB-2001			
		NAME VERTICAL SURFACE MOUNT HEADER ASSY, TIN CONTACTS, SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™			
0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -			
MATERIAL 		SIZE A2		CAGE CODE 00779	DRAWING NO C-1445053
SEE TABLE		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1
				REV C2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1445053-4](#)