


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	REVISED PER ECR-16-011494	20JUN2017	NK	CX





⚠ MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.

2 PLATING: CONTACTS- 2.54 μ m MINIMUM TIN LEAD OVER 1.27 μ m MINIMUM NICKEL.
HOLD DOWNS- 2.54 μ m MINIMUM TIN-LEAD OVER 1.27 μ m MINIMUM NICKEL.

△ 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.

5 PLATING: CONTACTS-2.54μm MINIMUM TIN OVER 1.27μm MINIMUM NICKEL.
HOLDDOWNS- 2.54μm MINIMUM TIN OVER 1.27μm MINIMUM NICKEL.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 03-OCT-2000		 TE Connectivity	
DIMENSIONS:		CHG K. WHITAKER 13-MAR-2001		NAME RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. WHITAKER 13-MAR-2001			
mm		PRODUCT SPEC 108-1836			
		APPLICATION SPEC 114-13000			
0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±		WEIGHT -		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL 		FINISH SEE TABLE		A200779C-1445057 -	
CUSTOMER DRAWING				SCALE	5:1
				SHEET	1 OF 1
				REV	C3

PCB LAYOUT COMPONENT SIDE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1445057-0](#)