








Bestückungsplan / contact layout

■ bestückt / assembled



Leiterplatten-Lochbild Vorschlag / PCB drillhole pattern proposal



Elastische Einpresszone / compliant pressfit zone

Isolierwerkstoff / housing material: PBT GF30

Bauart 7 / type 7

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062 / Nr. 10

diameter of drilled hole see drawing 164062 / No. 10

1) $\varnothing 1.6^{+0.09}_{-0.06}$ Durchmesser des metallisierten Loches

$\varnothing 1.6^{+0.09}_{-0.06}$ Diameter of finished plated-through hole

Copyright by ERNI GmbH
Proprietary notice pursuant to GO 40/01s to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale 2:1			
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation Federleiste D 32 EE <i>Fem. Connector D 32 Pressfit</i>			
				ERNI		www.ERNI.com		354442			
c		23.04.2013						Class STVD			
Index		Date									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[354442](#) [354442-E](#)