




REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	C3	REVISED PER ECR-16-011494	20JUN2017	NK	CX



2 PLATING: CONTACTS- 2.54μm MINIMUM TIN LEAD OVER 1.27μm MINIMUM NICKEL.
HOLDDOWNS- 2.54μm MINIMUM TIN-LEAD OVER 1.27μm MINIMUM NICKEL.

5 PLATING: CONTACTS-2.54μm MINIMUM TIN OVER 1.27μm MINIMUM NICKEL.
HOLDDOWNS- 2.54μm MINIMUM TIN OVER 1.27μm MINIMUM NICKEL.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 03-OCT-2000		 TE Connectivity	
		CHK K. WHITAKER 13-MAR-2001			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™	
mm		0 PLC ± 1 PLC ±0.13 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH			
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000			
MATERIAL		WEIGHT -			
 SEE TABLE		CUSTOMER DRAWING		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C-1445057	
				RESTRICTED TO -	
				SCALE 5:1	
				SHEET 1 OF 1	
				REV C3	

PCB LAYOUT COMPONENT SIDE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1445057-8](#)