




LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECR-16-011506	23JUN2017	NK	CX



- 1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
- 2 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 5 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.

	33.00	28.70	33.00	40.14	12	3-1445089-2
	30.00	25.70	30.00	37.14	11	3-1445089-1
	27.00	22.70	27.00	34.14	10	3-1445089-0
	24.00	19.70	24.00	31.14	9	2-1445089-9
	21.00	16.70	21.00	28.14	8	2-1445089-8
	18.00	13.70	18.00	25.14	7	2-1445089-7
	15.00	10.70	15.00	22.14	6	2-1445089-6
	12.00	7.70	12.00	19.14	5	2-1445089-5
	9.00	4.70	9.00	16.14	4	2-1445089-4
	-	-	6.00	13.14	3	2-1445089-3
	-	-	3.00	10.14	2	2-1445089-2

SUPERSEDED BY 3-1445089-2		33.00	28.70	33.00	40.14	12	+1445089-2-
SUPERSEDED BY 3-1445089-1		30.00	25.70	30.00	37.14	11	+1445089-1-
SUPERSEDED BY 3-1445089-0		27.00	22.70	27.00	34.14	10	+1445089-0-
SUPERSEDED BY 2-1445089-9		24.00	19.70	24.00	31.14	9	+445089-9-
SUPERSEDED BY 2-1445089-8		21.00	16.70	21.00	28.14	8	+445089-8-
SUPERSEDED BY 2-1445089-7		18.00	13.70	18.00	25.14	7	+445089-7-
SUPERSEDED BY 2-1445089-6		15.00	10.70	15.00	22.14	6	+445089-6-
SUPERSEDED BY 2-1445089-5		12.00	7.70	12.00	19.14	5	+445089-5-
SUPERSEDED BY 2-1445089-4		9.00	4.70	9.00	16.14	4	+445089-4-
SUPERSEDED BY 2-1445089-3		-	-	6.00	13.14	3	+445089-3-
SUPERSEDED BY 2-1445089-2		-	-	3.00	10.14	2	+445089-2-


FINISH	DIM Z	DIM V	DIM T	DIM W	NO. OF POSN	PART NUMBER
--------	-------	-------	-------	-------	----------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 09OCT2000		 TE Connectivity	
		CHK K. WHITAKER 17-APR-2001			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RIGHT ANGLE THRU HOLE HEADER ASSY, 0.38 MIC GOLD CONTACTS, WITH PLASTIC HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™	
		APVD C. JONES 17-APR-2001			
		PRODUCT SPEC -			
		APPLICATION SPEC -			
MATERIAL		WEIGHT -		SIZE A2	CAGE CODE 00779
 SEE TABLE -		FINISH		DRAWING NO C-1445089	RESTRICTED TO -
				SCALE 5:1	SHEET 1
				OF 2	REV A2


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		-	SEE SHEET 1	-	-	-

D


C



PCB LAYOUT FOR 2 POSITION 
COMPONENT SIDE



PCB LAYOUT FOR 3 POSITION 
COMPONENT SIDE



PCB LAYOUT FOR 4-12 POSITION 
COMPONENT SIDE

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 09OCT2000	 TE Connectivity			
		CHK K. WHITAKER 17-APR-2001				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 17-APR-2001	NAME			
	0 PLC ±-	PRODUCT SPEC	RIGHT ANGLE THRU HOLE HEADER ASSY, 0.38 MIC GOLD CONTACTS, WITH PLASTIC HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™			
	1 PLC ±-	-				
	2 PLC ±0.13	APPLICATION SPEC				
	3 PLC ±-	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ±-	WEIGHT	A2	00779	C-1445089	-
	ANGLES ±-					
MATERIAL	FINISH		CUSTOMER DRAWING			
	SEE TABLE -		SCALE	5:1	SHEET	2 OF 2
					REV	A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1445089-9](#)