





LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
		C		REVISED PER ECO-12-000118	17JAN12	KH	DY	



- REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- MATERIAL:
CONTACT AND SHIELD - PHOSPHOR BRONZE
HOUSING - GLASS FILLED POLYESTER, UL 94V-0.
- FINISH: SIGNAL AND GROUND CONTACTS:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5 µm MIN BRIGHT TIN-LEAD OVER BASE PLATING
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- THE TWO GROUNDS IN EACH COLUMN ARE COMMONED.
- CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- REFER TO "CONTACT LAYOUT" CHART FOR SEQUENCING.



⊕ Ø0.05Ⓢ X Y
ALL PLATED THRU HOLES

CONTACT LAYOUT										
A = 3.80mm (DIM M) B = 5.30mm (DIM M) G = GROUND										
ROWS	COLUMNS									
		10	9	8	7	6	5	4	3	2 1
	A	A	B	B	B	B	B	B	B	A
	B	A	B	B	B	B	B	B	B	A
	BG	G	G	G	G	G	G	G	G	G
	C	A	B	B	B	B	B	B	B	A
	D	A	B	B	B	B	B	B	B	A
	DG	G	G	G	G	G	G	G	G	G

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	S. J. MAGARO	12JUN2003	1469334-1		
				CHK	R. PATTERSON	12JUN2003	PART NUMBER		
				APVD	R. PATTERSON	17AUG2007			
DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	TE Connectivity		
mm				9 PLC ±		PRODUCT SPEC	HEADER ASSEMBLY, 2 PAIR, SELECTIVELY LOADED, 2.5mm TAIL, 25mm, HMZd		
				1 PLC ±		APPLICATION SPEC			
				3 PLC ±		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				4 PLC ±		WEIGHT		A100779C=1469334	
				ANGLES ±		CUSTOMER DRAWING	SCALE	8:1	SHEET 1 OF 1 REV C
MATERIAL				FINISH					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1469334-1](#)