





LOC	DIST	REVISIONS				
		F	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	H2	REV PER	ECO-10-001916	02FEB2010	JY SY
		J	ECR-10-018652		10SEP10	SW MQW

CONNECTOR ASSEMBLY
EXAMPLARY LOADED



CONTACT DIMENSIONS


SCALE 5:1



CONTACT LAYOUT

	z	a	b	c	d	e	f
1	C	A	A	A	A	A	C
2	C	A	A	A	A	A	C
3	C	A	A	A	A	A	C
4	C	A	A	A	A	A	C
5	C	A	A	A	A	A	C
6	C	A	A	A	A	A	C
7	C	A	A	A	A	A	C
8	C	A	A	A	A	A	C
9	C	A	A	A	A	A	C
10	C	A	A	A	A	A	C
11	C	A	A	A	A	A	C
GUIDING							

RECOMMENDED PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN



PLATED THRU HOLES PARAMETERS

REFERENCE APPLICATION SPECIFICATION

OBSOLETE 14	2 3 15	3-106081-0
	2 6 13	1-106081-9
	2 5 13	106081-9
	2 4	106081-4
	2 3	106081-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B CARBO 24JAN05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		CHK G SKIPPER 24JAN05	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLD ± 1-PLD ±0.2 2-PLD ±0.02 3-PLD ±0.005 4-PLD ± ANGLES ± ±0.30°		APVD G SKIPPER 24JAN05	PRODUCT SPEC 108-19082	
MATERIAL 1		SEE TABLE	APPLICATION SPEC 114-19029	
CUSTOMER DRAWING		WEIGHT -	SIZE A1	
SCALE 4:1		SHEET 1 OF 2		REV J

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

F

LTR

DESCRIPTION

DATE

DWN

APVD

—

—

SEE SHEET 1

—

—

—

1

MATERIAL:
CONTACT: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.

2

GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION
PIN: 0.5µm MIN TIN\LEAD.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.

4

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 1.

5

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
CENTRAL OFFICE APPLICATIONS.

6

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
UNCONTROLLED ENVIROMENT APPLICATIONS.

7

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.

8

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.

9

FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".

10

FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".

11

TO BE MEASURED AT BOTTOM OF SHROUD.

12

LOCATION PEG.

13

CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

14

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

15

0.76µm MIN GOLD PLATING AT MATING SURFACES.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

B CARBO

24JAN05

CHK

G.SKIPPER

24JAN05

APVD

G.SKIPPER

24JAN05

DIMENSIONS:

mm

0-PLG

1-PLG

2-PLG

3-PLG

4-PLG

ANGLES

±

±0.2

±0.02

±0.005

±0.30°

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC

108-19082

APPLICATION SPEC

114-19029

MATERIAL

SEE SHEET 1

FINISH

SEE SHEET 1

WEIGHT

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

©=106081

—

CUSTOMER DRAWING

SCALE

4:1

SHEET

2

OF

2

REV

J

Tyco

Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

MALE ASSEMBLY, Z-PACK 2mm HM,
TYPE C

AMP 4805 REV 31MAR2000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-106081-9](#)