



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-11-005030	12MAR2011	RK	HMR
	C3	REVISED PER ECO-13-016087	14OCT2013	DD	MB



1 FINISH: PLATED 0.00076 MIN THICK GOLD IN MATING AREA WITH 0.0025 MIN THICK TIN IN WIRE CRIMP AREA, ALL OVER 0.002 MIN THICK NICKEL,

2 FINISH: PLATED 0.00076 MIN THICK GOLD IN MATING AREA, PLATED 0.00038 MIN THICK GOLD IN SHUNT CONTACT PLATING AREA WITH 0.0025 MIN THICK TIN IN WIRE CRIMP AREA, ALL OVER 0.002 MIN THICK NICKEL.

3 GOLD FLASH THIS AREA PROVIDED FOR VISUAL INDICATION THAT TERMINAL IS GOLD PLATED.


4 PART LUBRICATED WITH CHEMLUBE 1102









5 FEATURE ON CARRIER STRIP IS RAISED ON GOLD PLATED PRODUCT. FEATURE APPEARS ADJACENT TO EVERY OTHER CONTACT MIN.

6 SEE FIGURE 1 FOR REELING DIRECTION.

7 SEE FIGURE 2 FOR REELING DIRECTION.

8. FOR LEVER ASSISTED CONNECTORS WITH SIDE SLIDE ACTION THE ALLOWABLE WIRE BRUSH LENGTH RANGE IS 0.10-0.70MM.



			22	1326028-8
			18-20	1326028-7
		22	1326028-6	
		18-20	1326028-5	
			22	1326028-4
			18-20	1326028-3
		22	1326028-2	
		18-20	1326028-1	
REELING	LUBRICATION	FINISH	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. R. SHUEY 02SEP99	TE Connectivity	
		CHK J. M. MYER 02SEP99		
		APVD K. DENLINGER 02SEP99	NAME	
		PRODUCT SPEC 108-2220	CONTACT, FEMALE, 0.64mm GOLD PLATED	
		APPLICATION SPEC 114-13006		
		WEIGHT -		
		Customer Drawing		
		SCALE 10:1		
		SHEET 1 OF 1		
		REV C3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1326028-5](#)