







LOC		DIST		REVISONS			
P	F	LTR	DESCRIPTION	DATE	DWN	T	APVD
	B		REV PER ECR 10-018921	13SEPT10	JR		TM



SECTION B-B



SECTION A-A
SCALE 10:1



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 THICK P.C. BOARD

3.81	.150		
2.54	.100		
2.03	.080	44.32	1.745
1.91	.075	33.78	1.330
1.57	.062	26.67	1.050
1.52	.060	19.05	.750
1.27	.050	17.27	.680
0.38	.015	12.83	.505
0.25	.010	12.70	.500
0.13	.005	9.14	.360
0.08	.003	7.37	.290
0.00127	.000050	6.35	.250
0.00076	.000030	4.06	.160
MM	IN	MM	IN
CONVERSION TABLE			

1. PARTS COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-5.

△ CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES,BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.

3 FLAMMABILITY V2 FOR THICKNESS 0.38mm, 1.5mm, qnd 3.0mm PER IEC 60695-11-10.

4 GLOW-WIRE FLAMMABILITY (GWFI) 800°C FOR THICKNESS 0.38mm AND 0.75mm PER IEC 60695-2-12.

5 GLOW-WIRE FLAMMABILITY (GWFI) 960°C FOR THICKNESS 1.5mm AND 3.0mm PER IEC 60695-2-12.

6 GLOW-WIRE IGNITION (GWIT) 825°C FOR THICKNESS 0.38mm, 0.75mm, 1.5mm AND 3.0mm PER IEC 60695-2-13.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN K. WHITAKER CHK D. COLEY APVD D. COLEY	14MAR2008 14MAR2008 14MAR2008	Tyco Electronics Corporation Harrisburg, Pa 17105-3608						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SOCKET HEADER ASSEMBLY, RIGHT ANGLE MOUNT,4 POSITION, UNIVERSAL MATE-N-LOK(TM)						
		0 PLC ± -		PRODUCT SPEC								
		1 PLC ± -		APPLICATION SPEC								
		2 PLC ± 0.13										
		3 PLC ± -										
4 PLC ± -		ANGLES ± -		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —		A1		00779	C=1586896	—		
CUSTOMER DRAWING						SCALE		4:1	SHEET	1 OF 1	REV	B

METRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1586896-1](#)