

VIEW B ROTATED 180°

POST FEED 40 mm STROKE	POST FEED 30 mm STROKE	PRE FEED 30 mm STROKE	PRE FEED 40 mm STROKE

LOC
A
DIST
66



QTY REQD PER ASSY				PARTS LIST			
		DIMENSIONS: mm [INCHES]		MATL	HT TR	FIN	
		DO NOT SCALE PRINT.		-	-	-	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		-	-	-	
		1 PLC DEC ±		DR M. CLIFFORD	APP 11DEC02	F. BACKHURST	
		2 PLC DEC ±		CHK -	REL 19FEB03	AMP AMP Incorporated	
3 PLC DEC ±				L. LOFTHOUSE	Harrisburg, PA 17105-3608		
BH	JUL03	ANGLES ±		NAME			MACHINE REF
L/JL	FEB03	SURF TEXTURE: ✓		SIDE FEED HD-I APPLICATOR			HD-I APPL
APP	DATE	REMOVE BURRS, BREAK SHARP EDGES RO. 38 MAX		SCALE	DWG NO	SHEET	
				-	D	1426400	1 OF 1
							REV B
		CAGE CODE	CUSTOMER AND ASSEMBLY DRAWING				RESTRICTED TO
		00779					-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426400-1](#)