



LOC DW	DIST /	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C1	REVISED (ECR-17-017717)	12DEC2017	T.Z.	H.W.

- NOTES:
1. MATERIAL:
- 1.1 HOUSING: SEE TABLE
- (PA66 WITH 30% G.F, UL94 V-0, BLACK COLOR.
OR LCP WITH 30% G.F, UL94 V-0, BLACK COLOR.
C1 OR PA66 WITH 30% G.F, UL94 V-0, WHITE COLOR.)
- 1.2 CONTACT: BRASS, T=0.25.
- 1.3 SHELL: SPCC.
- 1.4 REAR SHELL: SPCC.
- 1.5 SPRING: SPCC.
2. FINISH:
- 2.1 CONTACT:
- GOLD PLATING (SEE TABLE) ON CONTACT AREA,
2.54um [100u"] MIN. BRIGHT-TIN PLATING ON SOLDER TAIL AREA,
1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.
- 2.2 SHELL:
- 2.54um [100u"] MIN. BRIGHT-TIN PLATING,
1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.
- 2.3 REAR SHELL: 1.27um [50u"] MIN. NICKEL PLATING.
- 2.4 SPRING : 1.27um [50u"] MIN. NICKEL PLATING.
3. RECOMMENDED P.C.B THICKNESS :1.6mm.
4. WAVE SOLDER CAPABLE TO 265°C PER TE SPEC. 109-202, CONDITION B.
- THE SPRING IS OPTIONAL.






0.381um [15u"]	W/ O	PA66(BLACK)	1-1775468-2
	W/	PA66(BLACK)	1-1775468-1
C1	W/	PA66(WHITE)	1775468-3
	W/ O	LCP	1775468-2
GOLD FLASH	W/	PA66(BLACK)	1775468-1
	W/	PA66(BLACK)	1775468-1
MIN. GOLD THICKNESS	THE SPRING	HSG MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LEE 30MAR2007	TE Connectivity	
		CHK S. HOU 30MAR2007		
		APVD W.J. KE 30MAR2007	NAME	
		PRODUCT SPEC 108-57519	USB A TYPE, RECEPTACLE DUAL PORT, R/A, DIP CONNECTOR	
		APPLICATION SPEC		
		WEIGHT 5.31 GRAMS	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=1775468	RESTRICTED TO
			SCALE	SHEET 1 OF 2
				REV C1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC	± -
		1 PLC	± 0.3
		2 PLC	± 0.2
		3 PLC	± 0.15
		4 PLC	± -
		ANGLES	± 3°
MATERIAL		FINISH	
SEE NOTE		SEE NOTE	





RECOMMENDED P.C.B LAYOUT
TOP VIEW(TOLERANCE: ±0.05)



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
DW				SEE SHEET 1.		

NOTES:

1. DIMENSION:
TRAY: L= 270, W=235, H=25
SHIPPING CARTON: L= 485, W=280, H=210
2. QUANTITY: (SEE TABLE)
3. CARTON WEIGHT: (SEE TABLE)
4. PE BAGS SEALED AND ADD DESICCANT.



11.6	10.6	100	20	2000
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAYS/ CARTON	PCS/ CARTON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE TE Connectivity	
CHK		CHK			
APVD		APVD		NAME	
PRODUCT SPEC		PRODUCT SPEC		USB A TYPE, RECEPTACLE DUAL PORT, R/A, DIP CONNECTOR	
APPLICATION SPEC		APPLICATION SPEC		RESTRICTED TO	
WEIGHT		WEIGHT		SIZE CAGE CODE DRAWING NO	
CUSTOMER DRAWING		CUSTOMER DRAWING		A3 00779 C=1775468	
SCALE		SCALE		SHEET 2 OF 2	
REV C1		REV C1		REV C1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1775468-1](#)