

1

9.00

3

min.6

10

1.2^{+0.05}_{-0.10}

4

3.6

2

2.00

3.2^{+0.1}_{-0.3}

4.0

6

1.50

STE

STE

A

A

0.6±0.03

7

(10.5)

PCB

0.80

2.30

(3.1^{+0.1})

(1.6±0.2)

A-A

20:1

1.24±0.08

PCB-LAYOUT

Leiterplatten-Layout

5

2±0.05

NOTES:
BEMERKUNGEN:

1

1.27 μm - 2.54 μm Ni OVER THE COMPLETE LENGTH
1.27 μm - 2.54 μm Ni ueber die gesamte Laenge

2

0.8 μm - 1.8 μm Sn
0.8 μm - 1.8 μm Sn

3

1.0 μm - 3.0 μm Sn
1.0 μm - 3.0 μm Sn

4

Sn
Sn

5

RESTRING
UEBERSTAND
MIN. 50 μm

PLATED THROUGH HOLE SPECIFICATION
SPEZIFIKATION FUER DURCHPLATIERTE BOHRUNGEN

Cu THICKNESS KUPFER-SCHICHTDICKE	25-50 μm
Sn Pb-THICKNESS ZINN/BLEI SCHICHTDICKE	4-15 μm
DRILLED HOLE Ø1.10±0.025 BOHRLOCH Ø1.10±0.025	FINISHED HOLE Ø0.94 ^{+0.15} _{-0.15} PLATIIERTER LOCH Ø0.94 ^{+0.15} _{-0.15}

A2

6

DIMENSION OF LOOSE PIECE
Mass fuer Einzelteil

7

ACCORDING TO EXECUTION INSTUCTION AUDI NO. N 905 854
Nach Ausfuehrungsvorschrift AUDI Nr. N 905 854

8

TO BE REELED ON PANCAKE REEL WITH INTERLEAVING PAPER
Pappspulen mit Zwischenlagenpapier

9

TO BE REELED ON PLASTIC REEL WITH INTERLEAVING PAPER
Kunststoffspulen mit Zwischenlagenpapier

10

0.8 μm - 2.0 μm Au
0.8 μm - 2.0 μm Au

DIRECTION OFF
TOP OF REEL

1-2

1-3

2-2

2-3

8

9

2-1823233-3	A	Cu Sn 4	2 + 10 OVER ueber 1	9
2-1823233-2	A	Cu Sn 4	2 + 10 OVER ueber 1	8
1-1823233-3	A	Cu Sn 4	2 + 3 + 4 OVER ueber 1	9
1-1823233-2	A	Cu Sn 4	2 + 3 + 4 OVER ueber 1	8
TE PART NO	REV.	MATERIAL	SURFACE	REEL PACKAGING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
Allgemeintoleranz
n. ISO 8015
n. ISO 2768-MH-E

0-PLC	±
1-PLC	±0.2
2-PLC	±0.1
3-PLC	±
4-PLC	±
ANGLES	±1°
FINISH	-

MATERIAL

-

FINISH

-

DWN
P. Nickelfeld
CHK
J. Ryll

30OCT2008
30OCT2008

APVD
-

PRODUCT SPEC
108-18706

APPLICATION SPEC
114-18379

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME

TAB 1.5x0.6 WITH ACTION PIN
Flachstecker 1.5x0.6 mit ACTION PIN
-

SIZE

A2

CAGE CODE

00779

DRAWING NO

©=1823233

RESTRICTED TO

-

SCALE

10:1

SHEET

1 OF 1

REV

A2

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1823233-2](#)