




8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
20				20			
(C) COPYRIGHT 20				BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			
PART NUMBER	REV	FIRST USED	POWER UNIT		FEED TYPE	DESCRIPTION	
1852045-1	B	122500-1	LEADMAKER		POST FEED	CUTS CARRIER	
1852045-2	B	565435-5	BENCH MODEL K		PRE FEED	CUTS CARRIER	
1852045-3	B	354500-1	BENCH MODEL G		PRE FEED	CUTS CARRIER	
1852045-6	B	122500-1	LEADMAKER		POST FEED	CONTINUOUS CARRIER	
7-1852045-7	A	-	-		-	SPARE PARTS	






TERMINAL NAME: MALE METRI-PACK 280						
TE PN	MFG PN	DELPHI TERMINAL - DELPHI CRIMP SPECS				
286945	12129497					
-	-	PAD LTR	CRIMP HEIGHT		WIRE SIZE	
-	-	A	1.90±0.05mm [.075±.002]		3mm2	
-	-	B	1.65±0.05mm [.065±.002]		2mm2	
-	-	C	-		-	
-	-	D	-		-	
SEAL PN.	-					
1572716-1	12010293	CRIMP	SIZE		TYPE	RANGE
1572716-2	12015359					
1572716-3	15324980	WIRE	3.25mm [.128]		F	2-3mm2
-	-	INSUL	4.32mm [.170]		O	Ø2.80-3.49mm
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPL INSTRUCTIONS		SET UP GAGE	
4.90-5.28mm	NONE	15.88mm	408-8040		458637-	

- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
- △ APPLY TORQ-SEAL IN ALLEN SOCKET TO FILL HOLE AFTER FLAT HD HAS BEEN ADJUSTED TO CORRECT HEIGHT AT QUALIFICATION. APPLY PN 1-23419-5 LOC-TITE TO THREADS.



FEED TRACK POSITION



-	2	2	2	2	-	-	354779-8	PIN, WIRE DISC, .3030	127
-	2	2	2	2	-	-	8-354778-9	PIN, WIRE DISC, .2940	126
-	-	-	REF	-	-	-	455749-1	GUARD WINDOW	116
-	-	REF	-	-	-	-	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	-	1-21003-9	SCR, FLT SKT HD CAP 6-32 X .375	57
-	1	1	1	1	-	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	-	2-21000-8	SCR, SKT HD CAP 8-32 X .625	53
-	1	1	1	1	-	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	-	690753-1	SPACER, TONKER	50
-	-	1	-	-	-	-	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	1	-	-	-	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	-	-	-	690501-4	CAM, POST-FEED 1 5/8	47
-	1	1	1	1	-	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
-	1	1	1	1	-	-	690191-1	PLUG, NYLON	45
-	1	1	1	1	-	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	-	1-690142-0	DISC, INSULATION	38
-	1	1	1	1	-	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	-	690212-1	POST, RAM	35
-	1	1	1	1	-	-	690786-6	TERMINAL SUPPORT	34
-	2	2	2	2	-	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	-	1320908-2	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	-	1633091-7	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	-	1-455888-6	SPACER, CRIMPER	28
-	1	1	1	1	-	-	1320928-5	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	-	690472-2	STRIPPER	22
-	1	1	1	1	-	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	-	679625-2	SHEAR HOLDER, FRONT (NO CUT)	17
-	1	1	1	1	-	-	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	-	-	690461-2	STOP, SHEAR	11
-	-	1	1	1	-	-	1-690459-0	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	-	318707-2	FLOATING SHEAR, FRONT	9
1	1	1	1	1	-	-	1633381-5	ANVIL, COMBINATION	8
-	1	1	1	1	-	-	2-240641-4	SPACER	7
-	1	1	1	1	-	-	318701-4	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	-	238011-8	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	-	-	7-683454-7	CRIMPER, INSULATION O	3
-	1	1	1	1	-	-	1-455888-6	SPACER, CRIMPER	2
1	1	1	1	1	-	-	3-1673600-2	CRIMPER, WIRE	1

-77	-6	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO
THIS IS A CUSTOMER DRAWING. IT IS THE CUSTOMER'S RESPONSIBILITY TO OBTAIN THE NECESSARY APPROVALS AND PERMISSIONS FROM THE CUSTOMER'S ORGANIZATION BEFORE ANY CHANGES ARE MADE TO THIS DRAWING.						DRAWN R.O. WILSON 24MAY2006	tyco Electronics	Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS: INCHES						CHKD R.O. WILSON 25MAY2006	NAME	SIDE FEED HDM APPLICATOR
TOLERANCES UNLESS OTHERWISE SPECIFIED:						APPROV T. ELBIN 26MAY2006	PRODUCT SPEC	-
3 PLC ±.01							APPLICATION SPEC	-
1 PLC ±.01							WEIGHT	-
3 PLC ±.001							CAGE CODE	00779
4 PLC ±.0001							DRAWING NO	1852045
ANGLES ±.0001							RESTRICTED TO	-
FINISH							SCALE	3:5
MATERIAL							SHEET	1 OF 1
CUSTOMER DRAWING							REV	B

CUSTOMER VIEWABLE ASSEMBLY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852045-6](#)