

4

3

2

1





THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

20

© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

LOC	DIST	REVISIONS				
		P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS. APP.
F	00		G	PRODUCT SPEC WAS 108-15384	11SEP2009	TC
			H	CLARIFICATION	05JUN2012	JT
			J	REMOVED REF OLIVE SHELL COLOR	12JAN2015	JT
			K	CORRECTED MISTAKEN TITLE	28JAN2015	JT



NOTES ON SHEET 2/2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS. IL EST SUSCEPTIBLE D'ETRE REVISE. CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS POUR OBTENIR LA DERNIERE REVISION.		DWN/DESSINE 16SEP2004 Thierry CORRIOU	TYCO ELECTRONICS France SAS BP 30039, 95301 CERGY-PONTOISE Cedex			
DIMENSIONS: mm		CHK/VERIFIE 16SEP2004 Yves PETRONIN	NAME TITRE SHELL ASSY, PLUG, EN4165, FLOAT, 1 CAVITY			
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES): 0 PLC/DEC: ±0.3 1 PLC/DEC: ±0.3 2 PLC/DEC: ±0.3 3 PLC/DEC: ± 4 PLC/DEC: ± ANGLES ±1		APVD/APPROUVE 16SEP2004 Miguel FURIO				
MATERIAL /MATIERE SEE TABLE ON SHEET 2/2		PRODUCT SPEC SPEC. PRODUIT 108-15349	SIZE FORMAT A3		CAGE CODE 00779	DRAWING NO No PLAN C=1577134
FINISH/FINITION SEE TABLE ON SHEET 2/2		APPLICATION SPEC SPEC. APPLICATION 114-15121	WEIGHT MASSE APPROX. 18,6 g		RESTRICTED TO RESERVE A -	
Customer Drawing		/PLAN CLIENT		UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 1:1	SHEET FEUILLE 1 OF DE 2
						REV K

4

3

2

1

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE



RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

20

© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

LOC	DIST	REVISIONS				
		P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.
F	00		-	SEE SHEET 1	-	-

PASSIVATED	STAINLESS STEEL	2	FLAT WASHER, LARGE	7
SILVER PLATE	STAINLESS STEEL	2	SELF LOCKING NUT 4/40	6
PASSIVATED	STAINLESS STEEL	2	COMPRESSION SPRING	5
PASSIVATED	STAINLESS STEEL	2	FLAT WASHER	4
SILVER PLATE	STAINLESS STEEL	2	SELF LOCKING NUT 4/40	3
PASSIVATED	STAINLESS STEEL	2	SPRING GUIDE	2
ANODIC OXIDATION HARD,	ALUMINUM ALLOY	1	SHELL	1
FINISH	MATERIAL	QTY	DESIGNATION	ITEM



1. MATES WITH SHELL PLUG 1577135-X SERIES
LOCKING SYSTEM TO BE PROVIDED BY THE CUSTOMER

2. NOMINAL PRELOAD FORCE: 51N
NOMINAL FULLY MATED FORCE: 97N

3. CONNECTOR FLOAT IN PANEL
- HORIZONTAL DIRECTION: $\pm 1 \text{ mm}$
- VERTICAL DIRECTION: $\pm 1 \text{ mm}$

4. ITEMS 6 & 7 ARE SUPPLIED UN-ASSEMBLED

5. MARKING PART NUMBER, DATE-CODE AND
MANUFACTURER LOGO AS SHOWN ON SHEET 1/2

6. RECOMMENDED TIGHTENING TORQUE FOR ITEM 6: 0,8mN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS. IL EST SUSCEPTIBLE D'ETRE REVISE. CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS POUR OBTENIR LA DERNIERE REVISION.		DWN/DESSINE Thierry CORRIOU	TYCO ELECTRONICS France SAS BP 30039, 95301 CERGY-PONTOISE Cedex		
DIMENSIONS: mm		CHK/VERIFIE Yves PETRONIN			
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES): 0 PLC/DEC: ± 0.3 1 PLC/DEC: ± 0.3 2 PLC/DEC: ± 0.3 3 PLC/DEC: $\pm$ 4 PLC/DEC: $\pm$ ANGLES ± 1		APVD/APPROUVE Miguel FURIO	NAME TITRE SHELL ASSY, PLUG, EN4165, FLOAT, 1 CAVITY		
MATERIAL /MATIERE		PRODUCT SPEC SPEC. PRODUIT 108-15349			
FINISH /FINITION		APPLICATION SPEC SPEC. APPLICATION 114-15121	SIZE FORMAT A3		
		WEIGHT MASSE APPROX. 18,6 g			
		Customer Drawing /PLAN CLIENT	UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 1:1	SHEET FEUILLE 2 OF DE 2
					REV K

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1577134-4](#)