





- 1
- CONTACT AREA GOLD PLATED MIN. 0.8µm OVER MIN. 1.3µm Ni- LAYER
REST TIN PLATED MIN. 2µm
Kontaktzone vergoldet min. 0 0.8µm über min. 1.3µm Ni - Zwischenschicht
Rest verzinkt min. 1µm
- 2
- CONTACT AREA AND TOUCHING AREA TO CANTILEVER SPRING GOLD PLATED MIN. 0.8µm OVER MIN. 1.3µm Ni- LAYER, REST TIN PLATED MIN. 2µm
Kontaktzone und Anlagefläche zur überfeder vergoldet min. 0.8µm über min. 1.3µm Ni - Zwischenschicht, rest verzinkt min. 1µm
- 3
- CANTILEVER SPRING INSIDE AND OUTSIDE 0.8µm Au
überfeder inner und außen 0.8µm Au
- 4
- AFTER CUT-OFF FROM THE CARRIER STRIP
Nach trennen vom Trägerstreifen
- 5
- CURRENT LOADING MAX. 6A AT TU=25°C
Strombelastung max. 6A bei Tu=25°C
- 6
- BLADE THICKNESS 0.8± 0.03 DIN 46244
Messerstarke 0.8± 0.03 DIN 46244
- 7
- OBSOLETE







FORM_A



FORM_B

SECTION C-C
Schnitt C-C



						SECTION A-A Schnitt A-A 		SECTION B-B Schnitt B-B 		WIRE CRIMP Drahtcrimp 										
-	-	-								1.0mm±1.47 1.25mm±1.56 1.5mm±1.65										
-	-	-								Double Crimp Doppelanschlag										
929954-4		D	CuFe2		PRE-TINNED min. 1µm	1.0-1.5 FLR	max. 2.3	E = 2.8 G = 3.0 D _{Dr} = 1.3	H = 3.7 K = 3.9 D = 2.1 FORM B	0.35±0.75 0.35±1.0 0.50±0.50 0.50±0.75 0.50±1.0	878469-2	539635-1 with die set 539739-2	3.5	4.5	5.9					
929954-3		D																		
929954-2		D	CuSn4		PRE-TINNED min. 1µm															
929954-1		D																		
-	-	-	-	---																
929952-8		D	CuFe2			0.5-1.0 FLR	max. 2.0	E = 2.6 G = 2.8 D _{Dr} = 1.2	H = 3.2 K = 3.4 D = 1.8 FORM A	0.5mm±1.18 0.75mm±1.27 1.0mm±1.36	878468-2	539635-1 with die set 539739-2	3	3.9	6					
929952-7		D	CuSn4																	
929952-4		D	CuFe2		PRE-TINNED min. 1µm					Double Crimp Doppelanschlag										
929952-3		D								0.35±0.35 0.35±0.50 0.50±0.50										
929952-2		D																		
929952-1		D	CuSn4	PRE-TINNED min. 1µm																
-	-	-	-	-																
929950-4		C	CuFe2		PRE-TINNED min. 1µm	0.2-0.5 FLR	max. 1.6	E = 2.1 G = 2.1 D _{Dr} = 0.8	H = 2.8 K = 2.8 D = 1.4 FORM A	0.2mm±0.98 0.25mm±1.00 0.35mm±1.05 0.5mm±1.12	878467-2	539635-1 with die set 539739-2	2.5	3.75	5.9					
929950-3		C																		
929950-2		C																		
929950-1		C	CuSn4	PRE-TINNED min. 1µm																
-	-	-	-	-																
928939-4		G	CuFe2		PRE-TINNED min. 1µm	0.35-0.75 FLR	max 1.9	E = 2.3 G = 2.4 D _{Dr} = 1.0	H = 3.2 K = 3.1 D = 1.6 FORM A	0.35mm±1.09 0.50mm±1.16 0.75mm±1.27	878376-2	539635-1 with die set 539739-2	2.9	3.75	5.9					
928939-3		G								Double Crimp Doppelanschlag										
928939-2		G	CuSn4		PRE-TINNED min. 1µm					0.35±0.75										
928939-1		G																		
TE ORDER-NO. STRIP FROM Bandware	REV	MATERIAL Workstoff	SURFACE Oberflaeche	WIRE RANGE Drahtgrob- Bereich (mm²2)	INSULATION Isolations- Ø (mm)	STRIP FORM INSUL.-CRIMP Isol.- Crimp Bandware	WIRE CRIMP Drahtcrimp	WIRE CRIMP HEIGHT CH Drahtcrimp - Höhe CH	APPLICATION TOOL Anschlag-WKZ	HAND TOOL Handzange	EXTRACTION TOOL Ausdruckwerkzeug No. 5-1579007-5	A	B	C						
															CRIMP DIMENSION (mm) Crimp abmessungen (mm)					

THIS DRAWING IS NOT SUBJECT TO CONSTANT CHANGING SERVICE AND DOES NOT LAY CLAIM TO BE COMPLETE. FOR DEFINITE SPECIFICATION SEE RESPECTIVE TE CUSTOMER DRAWINGS. FURTHER VERSIONS ON INQUIRY.

Diese Zeichnung unterliegt nicht dem ständigen andienungsdienst und erhebt keinen anspruch auf vollständigkeit. verbindliche angaben sinder jeweiligen TE-kundenzeichnung zu entnehmen. weiter ausfuehrungen auf anfrage

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE: 29.12.04
BY: T. konieczny
CHK: M. Brunner
APPD: -

PRODUCT SPEC
108-18024
APPLICATION SPEC
114-18163
WEIGHT
-

NAME
Product Group Drawing for: Micro Timer 1 Contact
Produkt-Gruppen-Zeichnung for : Micro Timer 1 Kontakt
-

SIZE
A0

CASE CODE
-

DRAWING NO
1703333

RESTRICTED TO
-

CUSTOMER Drawing

SCALE
5:1

SHEET
1 of 1

REV
A4

STE

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[929952-1 \(Cut Strip\)](#) [929952-1 \(Loose Piece\)](#) [929952-1 \(Mouser Reel\)](#)