




**MATERIALS:**

HOUSING: HIGH TEMPERATURE NYLON, UL94 V-0  
EXTRACTOR: HIGH TEMPERATURE NYLON, UL94 V-0  
CONTACTS: COPPER ALLOY  
RETENTION BARB: BRASS, TIN PLATED

**INTERFACE FINISH:**

(1) 0.00038 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.  
(2) 0.00008 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.  
(3) 0.00076 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.

**FINISHED HOLE SIZE:** 0.15 MAXIMUM ANNULAR RING.

**KEEP OUT ZONE:**

**KEEP OUT AREA RESERVED FOR SOCKET EXTRACTORS, BOTH ENDS.**

**SOLDERTAIL FINISH:**

0.00300 MIN THK MATTE TIN OVER 0.00127 MIN THK NICKEL.

**LED LOCATION AS APPLICABLE PER CUSTOMER.**

**DATUM -G- IS CONNECTOR SIDE SURFACE OF PCB.**

|                                        |  |                                 |           |            |
|----------------------------------------|--|---------------------------------|-----------|------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>LEO ZHOU<br>28FEB2007    |           |            |
| DIMENSIONS:<br>mm                      |  | CHK<br>STEVEN YAO<br>28FEB2007  |           |            |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>STEVEN YAO<br>28FEB2007 | NAME      |            |
| 0 PLC ± -                              |  | PRODUCT SPEC                    | 108-2256  |            |
| 1 PLC ± 0.5                            |  | APPLICATION SPEC                | 114-13154 |            |
| 2 PLC ± 0.13                           |  | SIZE                            | CAGE CODE | DRAWING NO |
| 3 PLC ± 0.013                          |  | 114-13154                       | 00779     | 1932000    |
| 4 PLC ± 0.001                          |  | WEIGHT                          | —         | —          |
| ANGLES ± -                             |  | CUSTOMER DRAWING                | SCALE     | 4:1        |
| FINISH                                 |  | SHEET                           | 1         | OF 4       |
| 2 6                                    |  | REV                             | H7        |            |



8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.  
COPYRIGHT - By -

RELEASED FOR PUBLICATION  
ALL RIGHTS RESERVED.

LOC  
ES

DIST  
00

REVISONS

REV

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

1.35

LED PLACED IN "X" DIRECTION

2.10

LED PLACED IN "Y" DIRECTION

LED TARGET ZONE REF

4.25

PARTIAL BOTTOM VIEW

SCALE 12:1

1.23

LED HEIGHT OFF BOARD

2.10

LED PLACED IN "X" DIRECTION

1.35

LED PLACED IN "Y" DIRECTION

4.25

LED CENTER IN "X" OR "Y" DIRECTIONS

SECTION N-N

SCALE 10:1

|                |                 |                                           |                              |             |             |
|----------------|-----------------|-------------------------------------------|------------------------------|-------------|-------------|
| RETENTION BARB | BLACK           | BLACK                                     | 0.00076 MIN<br>(30u'')       | 2.54        | 7-1932000-6 |
|                | NATURAL         | BLACK                                     |                              | 2.54        | 7-1932000-5 |
|                | NATURAL         | BLUE<2935U>                               | 0.00038 MIN<15u''>           | 2.67        | 7-1932000-2 |
|                | NATURAL         | PINK<701C>                                | 0.00008 MIN<br>(3u'', FLASH) | 2.54        | 6-1932000-5 |
|                |                 | BLUE<284C>                                |                              | 2.54        | 6-1932000-4 |
|                | BLACK           | BLACK                                     | 0.00076 MIN<br>(30u'')       | 4.00        | 5-1932000-2 |
|                | NATURAL         | BLACK                                     |                              | 3.18        | 5-1932000-1 |
|                |                 |                                           |                              | 4.00        | 4-1932000-8 |
|                | NATURAL         | GREEN<368C><br>BLUE<284C><br>ORANGE<021C> | 0.00038 MIN<br>(15u'')       | 3.18        | 4-1932000-7 |
|                |                 |                                           |                              | 2.67        | 4-1932000-6 |
|                |                 |                                           |                              | 2.67        | 3-1932000-3 |
|                | NATURAL         | BLUE<284C><br>ORANGE<021C>                | 0.00038 MIN<br>(15u'')       | 2.67        | 2-1932000-5 |
|                |                 |                                           |                              | 2.67        | 2-1932000-1 |
|                |                 |                                           |                              | 3.18        | 1-1932000-7 |
|                | BLACK           | BLACK                                     | 0.00038 MIN<br>(15u'')       | 2.67        | 1-1932000-6 |
|                |                 |                                           | 0.00008 MIN<3u''>            | 4.00        | 1-1932000-5 |
| NATURAL        | BLACK           | 0.00038 MIN<br>(15u'')                    | 3.18                         | 1-1932000-1 |             |
|                |                 | 0.00008 MIN<3u''>                         | 2.67                         | 1-1932000-0 |             |
| NATURAL        | NATURAL         | 0.00038 MIN<br>(15u'')                    | 2.67                         | 1932000-7   |             |
|                |                 |                                           | 4.00                         | 1932000-6   |             |
|                |                 |                                           | 3.18                         | 1932000-5   |             |
|                |                 | 2.67                                      | 1932000-4                    |             |             |
|                |                 | 0.00008 MIN<br>(3u'', FLASH)              | 4.00                         | 1932000-3   |             |
|                |                 |                                           | 3.18                         | 1932000-2   |             |
|                |                 | 2.67                                      | 1932000-1                    |             |             |
| HOUSING STYLE  | EXTRACTOR COLOR | HOUSING COLOR                             | CONTACT GOLD INTERFACE       | TAIL LENGTH | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC ± -

1 PLC ± 0.5

2 PLC ± 0.13

3 PLC ± 0.013

4 PLC ± 0.0001

ANGLES ± -

MATERIAL -

FINISH -

DWN LEO ZHOU 28FEB2007

CHK STEVEN YAO 28FEB2007

APVD STEVEN YAO 28FEB2007

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

NAME

SIZE CAGE CODE DRAWING NO

RESTRICTED TO

TE Connectivity



SOCKET ASSEMBLY,  
VERTICAL DDR3 DIMM,  
SOLDER TAIL, 240 POSITION

A100779C1932000

SCALE 4:1 SHEET 2 OF 4 REV H7

4805 (3/11)









# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1932000-2](#)