

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-14-001886	12FEB2014	GK	HMR


REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2151397-6



FOR REPLACEMENT PARTS FOR APPLICATOR 1911174
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1911174

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	GOPALAKRISHNA HV		 TE Connectivity	
DIMENSIONS:		CHK	RAGHAVENDRA			
		APVD	RAGHAVENDRA		NAME SIDE FEED SYSTEM III APPLICATOR	
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			A3		©- 1911174	
FINISH		CUSTOMER DRAWING		SCALE	SHEET 1 OF 2	REV A1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		28
BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.				
COPYRIGHT 29				
PART NUMBER	REV	DESCRIPTION	PROGRAMMED MEMORY CHIP	
1911174-1	A	CUTS CARRIER	8-1911174-1	
1911174-6	A	CONTINUOUS CARRIER	8-1911174-6	
7-1911174-1	A	-1 AND SPARE PARTS	9-1911174-1	
7-1911174-6	A	-6 AND SPARE PARTS	9-1911174-6	
7-1911174-7	A	SPARE PARTS KIT	-	

APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	2.40mm [.094]	F
INSUL	3.60mm [.142]	O
APPL INSTRUCTIONS 408-10135		

WIRE SIZE		CRIMP HEIGHT mm [INCH]	
2mm ²		1.50±.05 [.059±.002]	
1.25mm ²		1.25±.05 [.049±.002]	
0.85mm ²		1.15±.05 [.045±.002]	

-	1	1	1	1	1-993111-6	PIN, SLOTTED SPRING 3.0 X 30.0	177
-	2	2	2	2	3-22280-7	SPRING, COMPRESSION	176
-	1	1	1	1	1752353-1	GUIDE PIN,HOLDDOWN	175
-	1	1	1	1	1901680-1	GUIDE PIN,HOLDDOWN	174
-	REF	REF	REF	REF	SEE TABLE	MEMORY CHIP, PROGRAMMED	135
-	1	1	1	1	1633565-1	DOCUMENTATION PACKAGE	71
-	1	1	1	1	1901048-1	TAG, IDENTIFICATION	67
-	2	2	2	2	21017-1	SCREW, DRIVE	66
-	1	1	1	1	18028-1	WASHER, FLAT, REG M3	64
-	1	1	1	1	1655785-9	SCR, BTN SKT HD CAP (M3 X 6)	62
-	2	2	2	2	1655785-1	SCR, BTN SKT HD CAP (M4 X 8)	60
-	1	1	1	1	985575-3	SCR, FLT SKT HD CAP M3 X 10.0	57
-	4	4	4	4	1655783-3	SCR, CAP, SOC HD, LOW HEAD, M4 X 12	54
-	1	1	1	1	1-18030-0	NUT, HEX, REG M3.5	52
-	1	1	1	1	1901681-1	HOLDDOWN, TERMINAL	51
-	1	1	1	1	1-1752354-8	STANDOFF,HOLD-DOWN	50
-	1	1	1	1	1752300-1	SF SYSTEM III APPLICATOR	46
-	1	1	1	1	1752308-1	RAM	44
-	1	1	1	1	2-1655785-3	SCR, BTN SKT HD CAP (M8 X 25)	41
-	1	1	1	1	993002-4	SCREW,SET,SFT TIP	40
-	1	1	1	1	1962043-1	PLUNGER,BALL,METRIC	39
-	1	1	1	1	1752309-2	RING, INSULATION CRIMP	38
-	1	1	1	1	1752356-3	SUPPORT, TERMINAL	34
-	2	2	2	2	3-1655785-3	SCR, BTN SKT HD CAP (M4 X 20)	33
-	1	1	1	1	18028-3	WASHER, FLAT, REG M5	32
-	1	1	1	1	5-1655316-3	SCR, SKT HD CAP, M5 X 10.0	31
-	1	1	1	1	1320908-2	SPACER, STRIP GUIDE	30
-	1	1	1	1	1901087-1	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	455888-3	SPACER, CRIMPER	28
-	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24
-	1	1	1	1	1976045-1	STRIPPER	22
-	1	1	1	1	18028-2	WASHER, FLAT, REG M4	20
-	REF	REF	REF	REF	1752311-1	STRIPPER	19
-	1	-	1	-	1338684-2	SHEAR HOLDER, FRONT	13
-	1	1	1	1	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	356885-5	STOP, SHEAR	11
-	-	1	-	1	1-1320921-0	SHEAR HOLDER, FRONT CUT	10
-	1	1	1	1	318707-1	FLOATING SHEAR, FRONT	9
1	2	2	1	1	1633620-1	ANVIL, COMBINATION	8
-	1	1	1	1	1338680-2	DEPRESSOR, SHEAR	5
-	1	1	1	1	238011-2	BLOCK, CRIMPER SPACER	4
1	2	2	1	1	7-1583690-2	CRIMPER, INSUL O	3
-	1	1	1	1	455888-6	SPACER, CRIMPER	2
1	2	2	1	1	3-1490019-3	CRIMPER, WIRE PREMIUM	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1911174-6](#)