



SECTION W-W



6
Ø 0.05 X Y
FINISHED HOLE SIZE
AND PLATED THRU HOLES

ROW A
ROW B
ROW C
ROW D
ROW E
ROW F
ROW G
ROW H
ROW I



○ = SIGNAL
⊗ = GROUND
RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303-1; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE). COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, 85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.

1934976-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J.K. SHOBER CHK C. RITIER APVD -	01JUL2008 01JUL2008 -
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME
mm	0 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	108-2303-1	HEADER ASSEMBLY, DOUBLE ENDED 3 PAIR, 10 COLUMN TinMan 85 OHM
MATERIAL	FINISH	APPLICATION SPEC	SIZE
-	-	114-13243	A100779
CUSTOMER DRAWING		WEIGHT	RESTRICTED TO
		-	-
		SCALE	SHEET
		8:1	1 OF 1
		REV	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1934976-1](#)