

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

COPYRIGHT




BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC




DIST

REVISIONS

| P | LTR | DESCRIPTION | DATE          | DWN       | APVD  |
|---|-----|-------------|---------------|-----------|-------|
|   | E1  | REVISED     | ECR-06-002095 | 20,JAN'06 | YH JK |
|   | E2  | REVISED     | ECR-06-002993 | 07,FEB'06 | YH JK |
|   | E3  | REVISED     | ECR-06-004324 | 13,SEP'06 | BS JK |




SPRING  
DIN X12CrNi177 K1350




|             |              |           |        |
|-------------|--------------|-----------|--------|
| 'Y'         | 2- 368028 -1 | TYPE B    | 1POST  |
| 'X'         | 1- 368028 -2 | TYPE A    |        |
| 'Y'         | 1- 368028 -1 |           |        |
| 'Z'         | 368028 -1    |           |        |
| TOP OF REEL | PART NUMBER  | REEL TYPE | REMARK |

DIRECTION OFF TOP OF REEL



Top of Reel 'X' Top of Reel 'Y' Top of Reel 'Z'

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:  
MM

MATERIAL

CuNiSi Alloy 0.4Thk.

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 <XX<10  $\pm 0.2$   
10 <XX<30  $\pm 0.25$   
30 <XX<100  $\pm 0.3$   
ANGLES  $\pm 3^\circ$

FINISH

PRE-TINNED

DWN

BS.YOO

CHK

YM.CHOI

APVD

JK SONG

PRODUCT SPEC

108-61041

APPLICATION SPEC

WEIGHT

NET. 1.02gf

CUSTOMER DRAWING

**tyco**  
ElectronicsAMP KOREA,  
kyungsan, korea

NAME

STANDARD POWER TIMER CONTACT  
FOR P.C.B - W/O LATCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

3 6 8 0 2 8

SCALE 10/1






SHEET

1


OF 2

REV E3

| LOC | DIST | REVISIONS |     |                  |      |     |      |
|-----|------|-----------|-----|------------------|------|-----|------|
|     |      | P         | LTR | DESCRIPTION      | DATE | DWN | APVD |
| DS  |      |           |     |                  |      |     |      |
|     |      |           |     | SEE SHEET 1 OF 2 |      |     |      |
|     |      |           |     |                  |      |     |      |



|                                                               |              |                |               |
|---------------------------------------------------------------|--------------|----------------|---------------|
| 'Y'                                                           | 1- 368028 -3 | TYPE A         | 2 POST        |
| 'X'                                                           | 0- 368028 -3 |                |               |
| TOP OF REEL                                                   | PART NUMBER  | REEL TYPE      | REMARK        |
| <b>tyco</b> AMP KOREA.<br>Electronics kyungsan, korea         |              |                |               |
| NAME<br>STANDARD POWER TIMER CONTACT<br>FOR P.C.B - W/O LATCH |              |                |               |
| SIZE                                                          | CAGE CODE    | DRAWING NO     | RESTRICTED TO |
| A3                                                            | 00779        | C= 3 6 8 0 2 8 |               |
| WEIGHT<br>NET. 1.06gf                                         |              | SCALE 10/1     | SHEET 2 OF 2  |
| CUSTOMER DRAWING                                              |              | REV E3         |               |



DIRECTION OFF TOP OF REEL

SEE SHEET 1 OF 2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

|                                  |                                                                     |
|----------------------------------|---------------------------------------------------------------------|
| DIMENSIONS:<br>MM                | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                           |
|                                  | 0 <XX<10 ± 0.2<br>10<XX<30 ± 0.25<br>30<XX<100 ± 0.3<br>ANGLES ± 3° |
| MATERIAL<br>CuNiSi Alloy 0.4Thk. | FINISH<br>PRE-TINNED                                                |

|                  |                           |
|------------------|---------------------------|
| DWN              | CHK                       |
| APVD             | PRODUCT SPEC<br>108-61041 |
| APPLICATION SPEC | WEIGHT<br>NET. 1.06gf     |
| CUSTOMER DRAWING |                           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-368028-2](#)