


-1	LEADMAKER				MECH POST FEED			
-2	BENCH MODEL K				MECH PRE FEED			
-3	BENCH MODEL G				MECH PRE FEED			
1	1	1	-	B	22594-8	NUT, HEX (1/2-20)		70
1	1	1	-	B	240628-1	PLATE, ADJUSTMENT		69
1	1	1	-	B	240626-1	SHAFT, PIVOT		68
1	1	1	-	B	240633-1	BUSHING		67
1	1	1	-	A	455680-1	LEVER, INTERMEDIATE		66
1	1	1	-	B	240629-1	BLOCK, PIVOT		65
1	1	1	-	A	240632-2	SCREW, ADJ FEED ROD		64
1	1	1	-	B	240659-3	PIN, CAM ROLLER		63
1	1	1	-	B	240658-1	ROLLER, CAM		62
1	1	1	-	B	454398-2	ROD, FEED		61
1	1	1	-	A	454178-1	GUIDE, FEED ROD		60
1	1	1	-	C	454220-1	CAP, RAM		59
1	1	1	-	D	454485-1	HOUSING		58
								57
1	1	1	-	B	690542-2	PAWL, FEED		56
1	1	1	-	B	240624-1	PIN, FEED FINGER		55
1	1	1	-	B	691499-1	SPRING, FEED FINGER		54
1	1	1	-	A	690541-1	HOLDER, FEED FINGER		53
1	1	1	-	B	455679-1	LEVER, TERMINAL FEED ARM		52
								51
								50
1	-	-	-	B	690602-6	CAM, PRE-FEED 1 5/8 ST		49
-	1	-	-	B	690602-5	CAM, PRE-FEED 1 1/8 ST		48
-	-	1	-	B	690501-4	CAM, POST-FEED 1 5/8 ST		47
								46
1	1	1	-	A	690191-1	PLUG, NYLON		45
1	1	1	-	C	455673-1	RAM		44
1	1	1	-	A	690125-1	WASHER, LAMINATED		43
1	1	1	-	A	690124-1	WASHER, RAM		42
1	1	1	-	A	690686-1	BOLT, CRIMPER (5/16x1.00)		41
1	1	1	-	A	23241-6	BALL, STEEL		40
1	1	1	-	A	690170-1	SPRING, COMPRESSION		39
1	1	1	-	C	690142-1	DISC, INSULATION		38
1	1	1	-	D	354777-1	WIRE DISC, PLASTIC		37
1	1	1	-	A	22480-5	WASHER, SPRING		36
1	1	1	-	B	690212-1	POST, RAM		35
								34
1	1	1	-	D	455675-9	PLATE, BASE		33
1	1	1	-	A	690432-3	SCREW, ADJUSTMENT		32
								31
1	1	1	-	B	455689-1	BLOCK, STRIP GUIDE ADJ		30
1	1	1	-	C	458144-1	PLATE, STRIP GUIDE		29
								28
2	2	2	-	A	1-22284-0	SPRING, DRAG		27
1	1	1	-	B	240793-1	LEVER, DRAG RELEASE		26
1	1	1	-	B	240792-1	DRAG, TERMINAL		25
1	1	1	-	D	7-690504-8	GUIDE, STRIP (REAR)		24
1	1	1	-	A	690438-1	GUIDE, STRIP (FRONT)		23
-	-	1	-	B	690472-2	STRIPPER		22
1	1	1	-	A	4-22284-9	SPRING, FEED RETURN		21
1	1	-	-	A	679218-1	STRIPPER WIRE STOP ASSY		20
1	1	-	-	B	458949-1	STRIPPER		19
1	1	1	-	B	189369-3	HOLDER, TERMINAL		18
1	1	1	-	A	691668-1	GUARD, CHIP (REAR)		17
1	1	1	-	B	318563-1	GUARD, CHIP, FRONT		16
1	1	1	-	B	690464-4	PLATE, SHEAR (REAR)		15
1	1	1	-	B	690462-1	HOLDER, SHEAR (REAR)		14
1	1	1	-	C	690463-1	SHEAR, FLOAT (REAR)		13
2	2	2	-	A	5-22280-0	SPRING, SHEAR		12
2	2	2	-	B	690461-1	STOP, SHEAR		11
1	1	1	-	C	690459-1	HOLDER, SHEAR (FRONT)		10
1	1	1	-	C	454276-1	SHEAR, FLOAT (FRONT)		9
1	1	1	-	C	1-662187-1	ANVIL		8
1	1	1	-	C	7-240641-4	SPACER, DEPRESSOR (REAR)		7
1	1	1	-	A	453393-3	DEPRESSOR, SHEAR (REAR)		6
1	1	1	-	C	1-455889-4	DEPRESSOR, SHEAR (FRONT)		5
1	1	1	-	B	238011-7	SPACER, BLOCK CRIMPER		4
1	1	1	-	C	1213077-4	CRIMPER, INSULATION		3
3	3	3	-	C	1-455888-2	SPACER, CRIMPER		2
1	1	1	-	C	5-456406-0	CRIMPER, WIRE		1
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO	
REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)								



		B	0150-8084-97	
		A	REVISED	
P	F	LTR	REVISION RECORD	

- 1 RECOMMENDED SPARE PARTS.
- 2 GREASE LIGHTLY.
- 3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
- 4 LUBRICATE DAILY USING NO. 20 MACHINE OIL.
- 5 CUT TO LENGTH AT ASSY
- 6 GUIDE OFF INSULATION BARREL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[680461-1](#)