

7022SJ=RLY, STD, OFF, 250 VDC

✓ ACTIVE

CII

TE Part # 4-1423164-9

TE Internal #: 7022SJ

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Knob**

Contact Current Rating: **10A@240VAC A**

Mode of Operation: **Off-Delay**

Multiple Timing Ranges: **Without**

Mounting Type: **Mounting Bracket**

Features

Product Type Features

Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays

Configuration Features

Multiple Timing Ranges	Without
------------------------	---------

Contact Features

Type of Control	Knob
Contact Current Rating	10A@240VAC A

Mechanical Attachment

Mounting Type	Mounting Bracket
---------------	------------------

Operation/Application

Mode of Operation	Off-Delay
-------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2019 (197)
Candidate List Declared Against: JAN 2019 (197)

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1423159-9
7012PB=RLY,STD,ON,2P,
125VDC, 5

Customers Also Bought

TE Part #324911-1
TERMINAL,SOLIS R 12-10
6 TAPE

TE Part #5394053001
100G0111-2.00-5

TE Part #1SNK916303R0000
JB16-3

TE Part #1SNK916310R0000
JB16-10

7022SJ=RLY, STD, OFF, 250 VDC

TE Part # 4-1423164-9
TE Internal #: 7022SJ



TE Part #6-1423162-2
7022CF=RLY,STD,OFF,2P,
480VAC,10MIN



TE Part #4-1423157-9
7012BFX=RLY,STD,ON,2P,
240VAC,



TE Part #8-1472969-6
7022PBX=RLY,STD,OFF,2P,
125V,5S,X OPT



TE Part #CQ10663001
100G0111-1.00-54



TE Part #CQ19753001
100G0111-2.00-54

Documents

Product Drawings

7022SJ=RLY, STD, OFF, 250 VDC

English

Datasheets & Catalog Pages

5-1773450-5_sec12_7000

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7022SJ](#)