

**ZDU 4/4AN****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |                                                                                              |
|------------|----------------------------------------------------------------------------------------------|
| Version    | Feed-through terminal, Tension-clamp connection, 4 mm <sup>2</sup> , 800 V, 32 A, dark beige |
| Order No.  | <a href="#">7904290000</a>                                                                   |
| Type       | ZDU 4/4AN                                                                                    |
| GTIN (EAN) | 4032248422197                                                                                |
| Qty.       | 50 pc(s).                                                                                    |

## ZDU 4/4AN

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 43 mm      | Depth (inches) | 1.693 inch |
| Depth including DIN rail | 43.5 mm    | Height         | 104.5 mm   |
| Height (inches)          | 4.114 inch | Width          | 6.1 mm     |
| Width (inches)           | 0.24 inch  | Net weight     | 21.32 g    |

## Temperatures

|                                  |                |                                  |                                                                                                   |
|----------------------------------|----------------|----------------------------------|---------------------------------------------------------------------------------------------------|
| Storage temperature              |                | Operating temperature range      | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
|                                  | -25 °C...55 °C |                                  |                                                                                                   |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C                                                                                            |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

## Rating data IECEx/ATEX

|                                |                                                                                                   |                                 |                   |
|--------------------------------|---------------------------------------------------------------------------------------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | DEMKO15ATEX1467U                                                                                  | Certificate No. (IECEX)         | IECEXULD15.0008U  |
| Max. voltage (ATEX)            | 550 V                                                                                             | Current (ATEX)                  | 28 A              |
| Wire cross section max. (ATEX) | 6 mm <sup>2</sup>                                                                                 | Max. voltage (IECEX)            | 550 V             |
| Current (IECEX)                | 28 A                                                                                              | Wire cross section max. (IECEX) | 6 mm <sup>2</sup> |
| Operating temperature range    | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7              |                   |
| Ex 2014/34/EU label            | II 2 G D                                                                                          |                                 | Ex eb II C Gb     |

## System specifications

|                               |                                                                                  |                                     |       |
|-------------------------------|----------------------------------------------------------------------------------|-------------------------------------|-------|
| Version                       | Tension-clamp connection, for plug-in cross-connector, One end without connector | End cover plate required            | Yes   |
| Number of levels              | 1                                                                                | Number of clamping points per level | 4     |
| Number of potentials per tier | 1                                                                                | Levels cross-connected internally   | No    |
| PE connection                 | No                                                                               | Rail                                | TS 35 |

## Additional technical data

|                             |         |                     |                 |
|-----------------------------|---------|---------------------|-----------------|
| Explosion-tested version    | Yes     | Installation advice | Direct mounting |
| Number of similar terminals | 1       | Open sides          | right           |
| Type of mounting            | Snap-on |                     |                 |

## CSA rating data

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1152892 | Current size B (CSA)          | 35 A   |
| Current size C (CSA)          | 35 A           | Current size D (CSA)          | 5 A    |
| Voltage size B (CSA)          | 600 V          | Voltage size C (CSA)          | 600 V  |
| Voltage size D (CSA)          | 600 V          | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

## ZDU 4/4AN

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|                                                                     |                                        |         |                      |
|---------------------------------------------------------------------|----------------------------------------|---------|----------------------|
| Blade size                                                          | 0.6 x 3.5 mm                           |         |                      |
| Clamping range, max.                                                | 6 mm <sup>2</sup>                      |         |                      |
| Clamping range, min.                                                | 0.13 mm <sup>2</sup>                   |         |                      |
| Connection cross-section, stranded, max.                            | 6 mm <sup>2</sup>                      |         |                      |
| Connection cross-section, stranded, min.                            | 0.5 mm <sup>2</sup>                    |         |                      |
| Connection direction                                                | top                                    |         |                      |
| Gauge to IEC 60947-1                                                | A4                                     |         |                      |
| Number of connections                                               | 4                                      |         |                      |
| Stripping length                                                    | 12 mm                                  |         |                      |
| Tube length for twin wire-end ferrule                               | Cross-section for conductor connection | nominal | 0.5 mm <sup>2</sup>  |
|                                                                     |                                        | min.    | 8 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 0.75 mm <sup>2</sup> |
|                                                                     |                                        | min.    | 8 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 1 mm <sup>2</sup>    |
|                                                                     |                                        | min.    | 8 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4    | Cross-section for conductor connection | nominal | 0.5 mm <sup>2</sup>  |
|                                                                     |                                        | min.    | 8 mm                 |
|                                                                     |                                        | max.    | 10 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 0.75 mm <sup>2</sup> |
|                                                                     |                                        | min.    | 6 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 1 mm <sup>2</sup>    |
|                                                                     |                                        | min.    | 6 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 1.5 mm <sup>2</sup>  |
|                                                                     |                                        | min.    | 8 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 2.5 mm <sup>2</sup>  |
|                                                                     |                                        | min.    | 8 mm                 |
|                                                                     |                                        | max.    | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 4 mm <sup>2</sup>    |
|                                                                     |                                        | min.    | 10 mm                |
|                                                                     |                                        | max.    | 12 mm                |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | nominal | 0.5 mm <sup>2</sup>  |
|                                                                     |                                        | nominal | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 0.75 mm <sup>2</sup> |
|                                                                     |                                        | nominal | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 1 mm <sup>2</sup>    |
|                                                                     |                                        | nominal | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 1.5 mm <sup>2</sup>  |
|                                                                     |                                        | nominal | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 2.5 mm <sup>2</sup>  |
|                                                                     |                                        | nominal | 12 mm                |
|                                                                     | Cross-section for conductor connection | nominal | 4 mm <sup>2</sup>    |
|                                                                     |                                        | nominal | 12 mm                |
| Twin wire-end ferrules, max.                                        | 1.5 mm <sup>2</sup>                    |         |                      |
| Twin wire-end ferrules, min.                                        | 0.5 mm <sup>2</sup>                    |         |                      |
| Type of connection                                                  | Tension-clamp connection               |         |                      |
| Wire connection cross section AWG, max.                             | AWG 10                                 |         |                      |

**ZDU 4/4AN**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data**

|                                                                                         |                     |
|-----------------------------------------------------------------------------------------|---------------------|
| Wire connection cross section AWG, min.                                                 | AWG 26              |
| Wire connection cross section, finely stranded, max.                                    | 6 mm <sup>2</sup>   |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.                                         | 6 mm <sup>2</sup>   |
| Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup> |

**General**

|                                         |                 |                                         |        |
|-----------------------------------------|-----------------|-----------------------------------------|--------|
| Installation advice                     | Direct mounting | Rail                                    | TS 35  |
| Standards                               | IEC 60947-7-1   | Wire connection cross section AWG, max. | AWG 10 |
| Wire connection cross section AWG, min. | AWG 26          |                                         |        |

**Rating data**

|                                 |                   |                                              |        |
|---------------------------------|-------------------|----------------------------------------------|--------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 800 V  |
| Rated current                   | 32 A              | Current at maximum wires                     | 41 A   |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 1 mΩ   |
| Rated impulse withstand voltage | 8 kV              | Power loss in accordance with IEC 60947-7-x  | 1.02 W |
| Pollution severity              | 3                 |                                              |        |

**UL rating data**

|                                         |        |                                            |        |
|-----------------------------------------|--------|--------------------------------------------|--------|
| Certificate No. (UR)                    | E60693 | Certificate No. (cURus)                    | E60693 |
| Conductor size Factory wiring max. (UR) | 10 AWG | Conductor size Factory wiring max. (cURus) | 10 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Conductor size Field wiring max. (UR)   | 10 AWG | Conductor size Field wiring max. (cURus)   | 10 AWG |
| Conductor size Field wiring min. (UR)   | 26 AWG | Conductor size Field wiring min. (cURus)   | 26 AWG |
| Current size B (cURus)                  | 30 A   | Current size C (UR)                        | 33 A   |
| Current size C (cURus)                  | 30 A   | Voltage size B (cURus)                     | 600 V  |
| Voltage size C (UR)                     | 600 V  | Voltage size C (cURus)                     | 600 V  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ECLASS 9.0  | 27-14-11-20 |
| ECLASS 9.1  | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |

Creation date September 18, 2022 3:35:03 AM CEST

**ZDU 4/4AN****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

**Technical data****Approvals**

Approvals



|                           |         |
|---------------------------|---------|
| ROHS                      | Conform |
| Certificate No. (UR)      | E60693  |
| Certificate No. (cURus)   | E60693  |
| Certificate No. (cURusEX) | E184763 |

**Downloads**

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">UKCA Ex Attestation of Conformity</a><br><a href="#">IECEX Certificate</a><br><a href="#">CB Test Certificate</a><br><a href="#">CB Certificate</a><br><a href="#">EAC certificate</a><br><a href="#">Lloyds Register Certificate</a><br><a href="#">EAC EX Certificate</a><br><a href="#">CCC Ex Certificate</a><br><a href="#">ATEX Certificate</a><br><a href="#">UKCA Ex Certificate</a><br><a href="#">Declaration of Conformity</a><br><a href="#">CE Declaration of Conformity all terminals</a><br><a href="#">UKCA Declaration of Conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Product Change Notification                 | <a href="#">PCN - EN</a><br><a href="#">PCN - DE</a><br><a href="#">PCN ZDU4 4AN ZPE4 4AN ATEX IECEX change</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">NTI ZDU/ZPE 4/4AN</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Brochures                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |

## ZDU 4/4AN

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold


Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7904290000](#)