




Elastische Einpresszone / *compliant pressfit zone*
 Isolierwerkstoff / *housing material*: PBT GF 30
 Anforderungsstufe 2 = 400 Steckzyklen / *performance class 2 = 400 mating cycles*
 Bauart 7 / *type 7*
 Lochaufbau siehe ERNI-Spezifikation 164062 / *hole design see ERNI-specification 164062*

- 1) $1.0^{+0.09}_{-0.06}$ Durchmesser des metallisierten Loches
 $1.0^{+0.09}_{-0.06}$ Diameter of finished plated-through hole

Leiterplatten-Layout Vorschlag PCB-Layout proposal



Information:	Tolerances	 All Dimensions in mm	Scale	2:1
			Designation	Federleiste D 32 EE Fem Connector D 32 Pressfit
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	 www.ERNI.com	354646	
			Class	STVD

Fehlende Masse und Angaben nach DIN EN 60603-2 / *Missing information and dimensions according to DIN EN 60603-2*
 Sonstige Angaben siehe Fertigungsunterlagen / *Additional indications please see the production documentation*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[354646](#)