


SERIES: TBL004V-508 | **DESCRIPTION:** TERMINAL BLOCK**FEATURES**

- 2~24 poles
- vertical with board
- interlocking (side)
- push button clamp
- 5.08 mm pitch
- UL safety approval
- IEC 60947-7-4 compliant

**SPECIFICATIONS**

parameter	conditions/description	min	typ	max	units
rated voltage (per contact)	UL			300	V
	IEC			320	V
rated current (per contact)	UL			10	A
	IEC			15	A
withstanding voltage	for 1 minute		1600		Vac
surge voltage				4000	V
contact resistance				20	mΩ
insulation resistance	at 500 Vdc	500			MΩ
operating temperature		-40		105	°C
safety approvals	UL 1059 certified, IEC 60947-7-4 compliant				
flammability rating	UL94V-0				
RoHS	yes				

SOLDERABILITY

parameter	conditions/description	min	typ	max	units
wave soldering	for maximum 5 seconds		250		°C

PART NUMBER KEY

TBL004V-508 - XX XX - 2XX					
Base Number		No. of Poles:	Body Color:	Push Button Color:	
02	10	18	*BE = blue	BE = blue	
03	11	19	GR = green	GR = green	
04	12	20	OR = orange	OR = orange	
05	13	21	YL = yellow	YL = yellow	
06	14	22	GY = gray	*GY = gray	
07	15	23	BK = black	BK = black	
08	16	24		WT = white	
09	17				

*Standard housing color is blue with gray push button. All other colors are subject to higher MOQ. Please inquire with CUI Devices sales for details.

MECHANICAL DRAWING


units: mm

tolerance:

 $X \leq 6.00$: ± 0.20 mm $6.00 < X \leq 10.00$: ± 0.30 mm $10.00 < X \leq 30.00$: ± 0.50 mm $30.00 < X \leq 60.00$: ± 0.70 mm $60.00 < X \leq 100.00$: ± 1.00 mm $100.00 < X \leq 160.00$: ± 1.30 mm $X > 160.00$: ± 1.60 mm

unless otherwise noted

DESCRIPTION	MATERIAL	PLATING/COLOR
housing	PA66 (UL94V-0)	
contacts	copper alloy	tin



WIRE ASSEMBLY		
	UL	IEC
Wire Range	24~14 AWG	0.2~1.5 mm ²
Strip Length	10 mm	

P.C.B. LAYOUT

This series is constructed of 1 pole modules where L is the total length, P is the pitch, and N is the number of poles.

N	02	03	04	05	06	07	08	09	10	11	12	13
L	12.66	17.74	22.82	27.90	32.98	38.06	43.14	48.22	53.30	58.38	63.46	68.54
B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
N	14	15	16	17	18	19	20	21	22	23	24	--
L	73.62	78.70	83.78	88.86	93.94	99.02	104.10	109.18	114.26	119.34	124.42	--
B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	--

REVISION HISTORY

rev.	description	date
1.0	initial release	08/13/2019
1.01	brand update	02/06/2020
1.02	updated datasheet	04/20/2020

The revision history provided is for informational purposes only and is believed to be accurate.

CUI DEVICES

CUI Devices offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI Devices reserves the right to make changes to the product at any time without notice. Information provided by CUI Devices is believed to be accurate and reliable. However, no responsibility is assumed by CUI Devices for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI Devices products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CUI Devices:

[TBL004V-508-02BE-2GY](#) [TBL004V-508-03BE-2GY](#) [TBL004V-508-04BE-2GY](#) [TBL004V-508-05BE-2GY](#) [TBL004V-508-06BE-2GY](#) [TBL004V-508-07BE-2GY](#) [TBL004V-508-20BE-2GY](#) [TBL004V-508-21BE-2GY](#) [TBL004V-508-22BE-2GY](#) [TBL004V-508-23BE-2GY](#) [TBL004V-508-24BE-2GY](#) [TBL004V-508-14BE-2GY](#) [TBL004V-508-15BE-2GY](#) [TBL004V-508-16BE-2GY](#) [TBL004V-508-17BE-2GY](#) [TBL004V-508-18BE-2GY](#) [TBL004V-508-19BE-2GY](#) [TBL004V-508-08BE-2GY](#) [TBL004V-508-09BE-2GY](#) [TBL004V-508-10BE-2GY](#) [TBL004V-508-11BE-2GY](#) [TBL004V-508-12BE-2GY](#) [TBL004V-508-13BE-2GY](#)