




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 60169-23
RPC-2.92 and SMA

Documents

Application note

AN001 "Calibration Services"

Documentation

This Part is delivered with:

- **USB Stick**
with S2p data file of the reference measurement values. Calibration Certificate as PDF file.
- **Calibration Certificate**
Details see "Declaration of calibration" options.

Material and plating

Connector parts

Center conductor - plug
Center conductor - jack
Outer conductor
Coupling nut
Dielectric
Substrate

Material

CuBe
CuBe
Stainless steel
Stainless steel
PEEK
Al₂O₃

Plating

Gold, min. 1.27 µm, over nickel
Gold, min. 1.27 µm, over nickel
Passivated
Passivated

Electrical data

Frequency range DC to 26.5 GHz
DC Resistance 50 Ω
Power handling ≤ 0.5 W

Electrical data (typical)

Return loss ≥ 32 dB, DC to 4 GHz
≥ 20 dB, 4 GHz to 26.5 GHz
Attenuation 40 dB ± 0.4 dB, DC to 4 GHz
40 dB ± 0.8 dB, 4 GHz to 26.5 GHz

Mechanical data

Mating cycles ≥ 500
Maximum torque 1.70 Nm
Recommended torque 0.90 Nm
Gauge 0.00 mm to 0.04 mm

Electrical verification standard

This Attenuator is designed as an electrical verification standard. Reference measurement values (calibration results) for transmission and reflection are included. Connected to a calibrated VNA the actual measured transmission and reflection values can be compared to the reference measurement values and the quality of the VNA calibration can be evaluated.

Environmental data

Operating temperature range¹ +20 °C to +26 °C
Rated temperature range of use² 0 °C to +50 °C
Storage temperature range - 40 °C to +85 °C

RoHS compliant

¹ Temperature range over which the reference measurement values are applicable.

² This range is underneath and above the operating temperature range, within the attenuator is fully functional and could be used without damage.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger																											
RPC-3.50		Attenuator Plug/Jack		03AS122-K40S3																											
Declaration of calibration options Factory Calibration Standard delivery for this verification standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results. Reflection results are traceable to national / international standards. A S2p data file with the reference measurement values is included. Accredited Calibration Not available. <i>For further, more detailed information see application note AN001 on the Rosenberger homepage.</i> Calibration interval Recommendation12 months Packing Standard1 pce in box Weight9.7 g/pce While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary. <table border="1"><tr><td>Draft</td><td>Date</td><td>Approved</td><td>Date</td><td>Rev.</td><td>Engineering change number</td><td>Name</td><td>Date</td></tr><tr><td>Kerstin Herzog</td><td>04.10.05</td><td>Markus Müller</td><td>25.10.16</td><td>i00</td><td>16-1390</td><td>Marion Striegler</td><td>25.10.16</td></tr></table><table border="1"><tr><td colspan="4">Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de</td><td colspan="2">Tel. : +49 8684 18-0 Email : info@rosenberger.de</td><td colspan="2">Page 3 / 3</td></tr></table>								Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date	Kerstin Herzog	04.10.05	Markus Müller	25.10.16	i00	16-1390	Marion Striegler	25.10.16	Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 3 / 3	
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date																								
Kerstin Herzog	04.10.05	Markus Müller	25.10.16	i00	16-1390	Marion Striegler	25.10.16																								
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 3 / 3																									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[03AS122-K40S3](#)