






Fully Compensated TR Series

The TR Series pressure transducer is a rugged, direct-media pressure monitoring solution designed for today's toughest pressure sensing environments.

The TR Series pressure transducer is a fully compensated, amplified output pressure sensor package combining Merit Sensor's Sentium process harsh media MEMS piezoresistive die with state-of-the-art pressure sensor ASIC signal management.

The TR Series "plug and play" design isolates onboard electronics from system media through an inert eutectic alloy solder bond of the MEMS pressure element to a ceramic PCB substrate. Direct media pressure sensing translates into excellent system design flexibility leading to lower cost and ease of manufacture.


The TR Series is designed for air, liquid and gas harsh media compatibility over a broad temperature range from -40°C (-40°F) to 150°C (302°F) with a total error band of less than 2.5%. The design includes a 4.7kohm pull-up resistor, operates on a single 5.0VDC supply, and requires no external components for proper operation. Both gage and absolute pressure reference designs up to 500 psi (35.5 bar) operating range are available.

*Standard Face Seal**Pins and Ferrule**Ferrule*

TYPICAL APPLICATIONS


- Industrial
 - HVAC system monitoring
 - Industrial automation
 - Process monitoring
 - Air-conditioning (refrigerant systems)
 - Portable measurement and analysis instrumentation
 - Water level and pressure monitoring
- Automotive
 - Transmission fluid pressure
 - Fuel system pressure
 - Oil system pressure
 - EGR system pressure
 - DEF system
 - Manifold absolute pressure
 - Fuel Rail system pressure
- Medical
 - Diagnostics and analysis equipment

TR Series Part Number Configurator




Features	Min.	Typ.	Max.	Unit	Notes
Electrical					
Supply Voltage (Vs)	4.5	5	5.5	Volts	
Supply Current			10	mA	
Output Current			2.5	mA	
Short Circuit Current	-25		25	mA	
Reverse Polarity Protection	-33			Volts	Device will cease operation during supply voltage fault.
Overvoltage Protection			33	Volts	Device will cease operation during supply voltage fault.
ESD	>4			kV	Human body model 1.5kOhm/100pF.
Performance					
Output Range (Vout)	10		90	%Vs	
Output Clipping Limit (Vout)	5		95	%Vs	
Resolution			0.02	%FS	>12 bit DAC
Accuracy	-2.5	0	2.5	%FS	Accuracy includes all error for hysteresis and linearity over the entire operating temperature range. It does not include lifetime drift. -40°C to 150°C.
Static Proof Pressure		2X FS		PSIA	
Burst Pressure		3X FS		PSIA	
Lifetime Drift	-0.5		0.5	%FS	1000 HRS. @ 150°C
Environmental					
Operating Temperature	-40		150	°C	
Storage Temperature	-55		150	°C	
Weight		1.08		Grams	Face Seal
		1.306		Grams	Ferrule
		1.179		Grams	Face Seal w/pins
		1.397		Grams	Face Seal w/pins

CROSS SECTION




PACKAGING AND SHIPPING



ELECTRICAL

Note: Power supply decoupling and output filtering included




Fully Compensated TR Series

DIMENSIONS FOR STANDARD OPTIONS (in millimeters)


Dimensions for reference only.

Engineering drawings (with tolerance) available upon order.


Standard Face Seal



Ferrule



Pins and Ferrule





Merit Sensor is based in Salt Lake City, Utah



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Merit Sensor:

[TR1-0100A-101](#) [TR1-0030A-001](#) [TR1-0030G-101](#) [TR1-0100G-001](#) [TR1-0030A-101](#) [TR1-0100G-101](#) [TR1-0015G-001](#) [TR1-0300G-001](#) [TR1-0015G-101](#) [TR1-0100A-001](#) [TR1-0300A-001](#) [TR1-0300G-101](#) [TR1-0300A-101](#) [TR1-0030G-001](#) [TR1-0015A-001](#) [TR1-0500A-101](#) [TR1-0500G-101](#) [TR1-0500A-001](#) [TR1-0015A-101](#) [TR1-0500G-001](#) [TR1-0030G-111](#) [TR1-0500G-111](#) [TR1-0030A-111](#) [TR1-0015A-111](#) [TR1-0300G-111](#) [TR1-0500A-111](#) [TR1-0015G-111](#) [TR1-0300A-111](#) [TR1-0100G-111](#) [TR1-0100A-111](#)