

# LOCTITE ECCOBOND UF 1173

June 2020

## PRODUCT DESCRIPTION

LOCTITE ECCOBOND UF 1173 provides the following product characteristics:

|                         |                                                                                                                                                                                                   |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Technology</b>       | Epoxy                                                                                                                                                                                             |
| <b>Appearance</b>       | Black liquid                                                                                                                                                                                      |
| <b>Cure</b>             | Heat cure                                                                                                                                                                                         |
| <b>Product Benefits</b> | <ul style="list-style-type: none"> <li>• One component</li> <li>• Void-free underfill</li> <li>• Low CTE</li> <li>• Long pot life</li> <li>• Dissipates stress away from solder joints</li> </ul> |
| <b>Application</b>      | 2nd Level Underfill                                                                                                                                                                               |

LOCTITE ECCOBOND UF 1173 is designed to provide a uniform and void-free encapsulant underfill, maximizing the device's temperature cycling capability, distributing stress away from solder connects thus enhancing solder joint reliability in CSP and BGA packages.

LOCTITE ECCOBOND UF 1173 material has been formulated without any reportable REACH SVHCs (current to June 2018) and the product is not CMR classified.

## TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity by Rheometer AR 1000, Pa-s:

|                                      |      |
|--------------------------------------|------|
| @ 10 s <sup>-1</sup>                 | 7.5  |
| Thixotropic Index                    | 0.71 |
| Density, g/cm <sup>3</sup>           | 1.69 |
| Pot Life @ 25°C, hours               | 48   |
| Shelf Life @ -40°C (estimated), days | 180  |
| Flash Point - See SDS                |      |

## TYPICAL CURING PERFORMANCE

### Cure Schedule

5 minutes @ 150°C

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

## TYPICAL PROPERTIES OF CURED MATERIAL

### Physical Properties

Coefficient of Thermal Expansion:

|                                              |       |
|----------------------------------------------|-------|
| Below Tg, ppm/°C                             | 26    |
| Above Tg, ppm/°C                             | 103   |
| Glass Transition Temperature (Tg) by TMA, °C | 160   |
| Storage Modulus, @ 25°C, DMA, MPa            | 6,000 |

### Electrical Properties

Dielectric Constant / Dissipation Factor :

|          |             |
|----------|-------------|
| @ 5 GHz  | 3.29/0.0179 |
| @ 10 GHz | 3.19/0.0176 |
| @ 20 GHz | 3.18/0.0191 |
| @ 30 GHz | 3.18/0.0197 |
| @ 40 GHz | 3.18/0.0243 |
| @ 50 GHz | 3.19/0.0360 |

## TYPICAL ENVIRONMENTAL RESISTANCE

### Outgassing Properties

Outgassing, NASA Outgassing:

|         |      |
|---------|------|
| TML, %  | 0.43 |
| CVCM, % | 0.02 |
| WVR, %  | 0.1  |

## GENERAL INFORMATION

**For safe handling information on this product, consult the Safety Data Sheet, (SDS).**

### THAWING:

1. This product is packed and shipped in dry ice packs to prevent excessive temperature exposure during shipping.
2. Allow material to reach room temperature before use.
3. After removing from the freezer, set the syringes to stand vertically while thawing.
4. Once material has reached room temperature, the adhesive should not be re-refrigerated.

### DIRECTIONS FOR USE

1. LOCTITE ECCOBOND UF 1173 can be applied by needle or jet dispense.
2. When applied by jetting, nozzle heating of 50 to 60°C is recommended.
3. For faster flow, board should be heated to 70 to 100°C.

### Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

## STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

## Optimal Storage : -40 °C +/- 3°C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

## Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\text{N} \times 0.225 = \text{lb/F}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{psi} \times 145 = \text{N/mm}^2$

$\text{MPa} = \text{N/mm}^2$

$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$

$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$

$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$

$\text{mPa}\cdot\text{s} = \text{cP}$

## Disclaimer

### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

### Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

## Reference 6

Americas  
+1.888.943.6535

Europe  
+32.1457.5611

Asia  
+86.21.2891.8000

**For the most direct access to local sales and technical support visit: [www.henkel.com/electronics](http://www.henkel.com/electronics)**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2420246](#) [2420247](#) [2840907](#) [2905491](#)