

OmniSmart 120V 1000VA 700W Line-Interactive UPS, Tower, Built-In Isolation Transformer, USB port

MODEL NUMBER: **OMNI1000ISO**



Highlights

- 1000VA / 1kVA tower 120V line interactive UPS with isolation transformer
- Corrects brownouts and overvoltages from 81V to 143V
- USB port, Normal and common mode EMI/RFI line noise immunity
- NEMA 5-15P input plug and 6 5-15R outlets

Package Includes

- OMNI1000ISO UPS System
- USB cable
- Instruction manual

Description

OMNI1000ISO offers complete UPS protection with built-in line-interactive voltage regulation, intelligent monitoring and unattended shutdown capability. Built-in isolation transformer with Faraday shield offers full isolation and complete common mode noise rejection. 1000VA power-handling capacity supports point-of-sale applications, computers, internetworking equipment and home theater systems during commercial power failures. Line-interactive voltage regulation corrects brownouts as low as 81V and overvoltages as high as 143V back to normal 120V levels, reserving battery power for use during complete power failures. USB communications port works with PowerAlert® software and cabling to provide automatic unattended shutdown of connected network and PC applications.

Features

- 1000VA line-interactive UPS with Faraday-shielded, low-impedance isolation transformer delivers full isolation from potential damage and performance problems
- Provides immunity from EMI/RFI line noise in both normal and common modes. Delivers clean signal-reference ground, reducing data errors and audio/video distortion
- Automatic voltage regulation (AVR) automatically corrects incoming voltage to keep equipment working through low voltage (brownouts) as low as 81V and overvoltages as high as 143V without consuming battery power
- Supports loads up to 1000VA/700W
- Half-load runtime of 24 min. (500VA/350W); full load runtime of 8 min. (1000VA/700W)
- 5 diagnostic LEDs indicate AC present, on battery, voltage correction status, overload and battery low/replace
- Electrostatic discharge (ESD) resistance reduces potential static damage to connected electronics
- USB port enables data-saving unattended shutdown when used with PowerAlert software, available via FREE download from tripplite.eaton.com/products/power-alert
- Built-in surge suppression (backed by \$200,000 Ultimate Lifetime Insurance U.S., Canada, and Puerto Rico only) safeguards connected equipment against damage
- SURGE VOLTAGE WITHSTAND CAPABILITY: ANSI/IEEE C62.41 Catagories A & B 6KV/200/500 amp 100Khz Ringwave and category B BiWave
- SURGE VOLTAGE ATTENUATION: N-G 2000:1, L-G 240:1, L-N 100:1
- INSERTION LOSS: 65 db N-G from 10Khz to 100Khz, 45 to 60 db L-G from 10Khz to 100Khz, 18 to 54 db L-N from 50Khz to 500 Khz

- 6 UPS-supported AC outlets; 6-ft. cord
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment

Specifications

OVERVIEW	
UPC Code	037332126931
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	7.6A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
OUTPUT	
Output Capacity (VA)	1000
Output Capacity (kVA)	1
Output Capacity (Watts)	700
Output Capacity (kW)	0.7
Output Capacity Details	5.8A @ 120V. 125% @ 10 minutes 110% +/- 10% @ 5 seconds
Power Factor	0.7
Nominal Voltage Details	120V in line mode and 115V battery
Frequency Compatibility	60 Hz
Frequency Compatibility Details	Output is regulated to +/-0.05Hz when input frequency exceeds +/-5Hz of nominal.
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R

Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	8 min. (700W)
Runtime Half Load (min.)	24 min. (350W)
Expandable Runtime	No
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	 RBC53
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 85 to 143
Overvoltage Correction	Input voltages between 128 and 143V are reduced by 9%
Undervoltage Correction	Input voltages between 96 and 107V are boosted by 10%
Severe Undervoltage Correction	Input voltages between 85 and 95V are boosted by 20%
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
ISOLATION	
Output Isolation Transformer	Professional grade load isolation transformer
Surge Voltage Withstand Capability	ANSI/IEEE C62.41 Categories A & B 6KV/200/500 amp 100Khz Ringwave and category B BiWave
Surge Voltage Attenuation	N-G 2000:1, L-G 240:1, L-N 100:1
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	510
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Tower



Powering Business Worldwide



Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary UPS Depth (mm)	234
Primary UPS Height (mm)	325
Primary UPS Width (mm)	191
Shipping Dimensions (hwd / in.)	16.90 x 13.50 x 11.30
Shipping Dimensions (hwd / cm)	42.93 x 34.29 x 28.70
Shipping Weight (lbs.)	46.10
Shipping Weight (kg)	20.91
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	32.51 x 19.05 x 23.37
UPS Power Module Dimensions (hwd, in.)	12.8 x 7.5 x 9.2
UPS Power Module Weight (kg)	16.51
UPS Power Module Weight (lbs.)	36.4
Unit Dimensions (hwd / in.)	12.750 x 7.500 x 9.250
Unit Weight (lbs.)	36.4000
Unit Weight (kg)	16.51
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 95%, non-condensing
AC Mode Efficiency Rating (100% Load)	91%
AC Economy Mode Efficiency Rating (100% Load)	0.91
Operating Elevation	0-6562 ft. (0-2000 m)
COMMUNICATIONS	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert software at https://tripplite.eaton.com/products/power-alert
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Insertion Loss	65 db N-G from 10Khz to 100Khz, 45 to 60 db L-G from 10Khz to 100Khz, 18 to 54 db L-N from 50Khz to 500 Khz
Network Management Card Description	Network management not supported



Powering Business Worldwide



Communications Interface	USB
LINE / BATTERY TRANSFER	
Transfer Time	6 milliseconds typical (10 milliseconds max)
Low Voltage Transfer to Battery Power (Setpoint)	81
High Voltage Transfer to Battery Power (Setpoint)	143
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries; Surge/noise protection
APPLICATIONS	
UPS Applications	High-End Desktop/Small Network; Retail/Point of Sale; Hospitality
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[OMNI1000ISO](#)