

USA-19HS Driver Installation

The USA-19HS is incompatible with Windows computers with Core Isolation / Memory Integrity enabled. These features will need to be disabled in order to install and use the USA-19HS driver.

Keyspan USB to Serial Adapter - USB-A Male to DB9 RS232 Male, 3 ft. (0.91 m), TAA

MODEL NUMBER: USA-19HS



Connects devices with a 9-pin serial port, such as switches, routers, barcode scanners and lab equipment, to your computer or laptop's USB-A port.

Features

Works with RS-232 Serial Devices Connects to switches, routers, barcode scanners, GPS units, point-of-sale devices, lab equipment, network storage devices, modems, graphics tablets and other devices with a DB9 serial port. Supports data transfer speeds up to 230 Kbps—twice as fast as a built-in serial port.

Easy to Set Up and Use Right Out of the Box

No external power supply is needed and only one connection is required. Simply connect the included three-foot (0.9-meter) USB cable between the unit's USB-B port and your computer's USB-A port. The unit is compatible with any USB cable up to 16 feet (4.9 meters). A green LED indicates data activity at a glance. The unit weighs only 2 ounces for convenient transport in a backpack or laptop bag.

Compatible with Major Operating Systems Works with Microsoft Windows (up to Windows 11) and macOS X (up to Ventura 13.3.1), and includes Windows line monitor and data trace software. The unit supports both 32-bit and 64-bit systems and has continuously updated drivers available for download on the unit's Technical Support page.

TAA-Compliant for GSA Schedule Purchases The USA-19HS is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

Highlights

- Supports data transfer speeds up to 230 Kbps to ensure reliable data transfers
- Detachable 3 ft. USB cable included
- Plug-and-play operation with no software required for easy, immediate installation
- Works with 32- and 64-bit Windows and macOS X (see [model support page](#))

System Requirements

- Computer with an available USB-A port
- Compatible with Windows 2000, XP, Vista, 7, 8, 10, 11, Windows 2008 Server R2, Windows Server 2012
- Compatible up to macOS Ventura 13.3.1

Note: Computer should have Administrator access to avoid potential installation issues when first installing drivers. When attempting to use most recent driver with an existing USA-19HS unit, it is critical that the old drivers be uninstalled from the computer before downloading and installing the newer driver. Even though the old driver no longer works, the Device Manager will still attempt to use it.

Package Includes

- USA-19HS Keyspan High-Speed RS232 to USB Adapter
- USB-A cable, 3 ft. (0.91 m)
- CD with driver software and Owner's Manual

OVERVIEW

UPC Code

672603000413



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Device Compatibility	Printer; Router; Scanner
Technology	USB
Country/Region	Global
Host Connector	USB A (MALE)
INPUT	
Bus Powered	Yes
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB9 (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	3.8mm
Wire Gauge (AWG)	28
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	36
Cable Length (cm)	30.48
Total Number of Ports	2
Shipping Dimensions (hwd / in.)	3.00 x 9.00 x 6.00
Shipping Dimensions (hwd / cm)	7.62 x 22.86 x 15.24
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	0.950 x 1.630 x 3.070
Unit Dimensions (hwd / cm)	2.42 x 4.13 x 7.81
Unit Dimensions (hwd / mm)	24.2 x 41.3 x 78.1
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Cable Compatibility	DB9 (Female)



Powering Business Worldwide



Driver Required	Yes
STANDARDS & COMPLIANCE	
Product Certifications	EN 55024; EN 55032
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[USA-19HS](#)