


UNCONTROLLED
DOCUMENT

29F0328-0T0-10

RoHS

PHYSICAL DIMENSIONS:

A	8.34 [.328]	± 0.12 [.005]
B	10.88 [.428]	± 0.15 [.006]
C	10.57 [.416]	± 0.20 [.008]
D	7.62 [.300]	± 0.13 [.005]
E	2.54 [.100]	± 0.05 [.002]
G	3.18 [.125]	± 0.38 [.015]
H	11.43 [.450]	\pm MAX




ELECTRICAL CHARACTERISTICS:


Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	342	
Minimum	257	
Maximum	427	10,000 mA

1. BULK PACKED 910 per CASE.
2. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
3. TERMINATION FINISH IS 100% TIN.
4. OPERATION TEMPERATURE (INCLUDING SELF-HEATING):
-40 ~ +125°C.

HOLE PATTERN FOR THRU-HOLE INSERTION



|Z|, R, AND X vs. FREQUENCY



DIMENSIONS ARE IN mm [INCHES]				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
D	ADD NOTE 4	08/30/12	QIU	PROJECT/PART NUMBER: 29F0328-0T0-10			
C	ADD ROHS SYMB. UPDATE LOGO	10/20/08	JRK				
B	UPDATE COMPANY LOGO	04/24/07	JRK				
A	ORIGINAL DRAFT	04/30/04	JRK				
REV	DESCRIPTION	DATE	INT				
				DATE:	04/30/04	SCALE:	NTS
				CAD #	29F0328-0T0-10-D-1	TOOL #	H0328
				REV	D	PART TYPE:	CNZ ASSEMBLY
						DRAWN BY:	TMB
						SHEET:	
						1 of 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[29F0328-OT0-10](#)