

**IE-FM5Z2LM0050LD0LD0-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |                                                                                       |
|------------|---------------------------------------------------------------------------------------|
| Version    | Patch cable, duplex clip included, LC-Duplex IP 20, LC-Duplex IP 20, 50 µm, LSZH, 5 m |
| Order No.  | <a href="#">2903650050</a>                                                            |
| Type       | IE-FM5Z2LM0050LD0LD0-X                                                                |
| GTIN (EAN) | 4099986026889                                                                         |
| Qty.       | 1 pc(s).                                                                              |

## IE-FM5Z2LM0050LD0LD0-X

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Length     | 5 m   | Length (inches) | 196.85 inch |
| Net weight | 500 g |                 |             |

## Temperatures

|                       |                |
|-----------------------|----------------|
| Operating temperature | -20 °C...70 °C |
|-----------------------|----------------|

## Cable specific standards

|                                                                  |             |                                                         |                               |
|------------------------------------------------------------------|-------------|---------------------------------------------------------|-------------------------------|
| Specification for checking the symmetrical communication cabling | IEC 61935-3 | Specification for twisted-pair device connection cables | IEC 61156-6, DIN EN 50288-4-2 |
|------------------------------------------------------------------|-------------|---------------------------------------------------------|-------------------------------|

## General standards

|                    |              |
|--------------------|--------------|
| Connector standard | IEC 61754-20 |
|--------------------|--------------|

## Standards

|                    |              |
|--------------------|--------------|
| Connector standard | IEC 61754-20 |
|--------------------|--------------|

## Fibre-optic

|             |                                         |           |                                                  |
|-------------|-----------------------------------------|-----------|--------------------------------------------------|
| Attenuation | ≤ 1.5 dB at 1300 nm, ≤ 3.5 dB at 850 nm | Bandwidth | ≥ 500 MHz*km at 1300 nm, ≥ 1500 MHz*km at 850 nm |
| Fibre type  | GOF, Multimode, OM4                     |           |                                                  |

## Cable structure

|                       |            |                  |         |
|-----------------------|------------|------------------|---------|
| Cable layout          | ZIPCORD    | Core diameter    | 50 µm   |
| Material sheath       | LSZH       | Primary coating  | 245 µm  |
| Sheath diameter       | 2 * 1.5 mm | Sheathing colour | Magenta |
| Standard designations | I-V(ZN)H   |                  |         |

## Mechanical and material properties of cable

|                                 |                     |                                |                     |
|---------------------------------|---------------------|--------------------------------|---------------------|
| Halogen                         | No                  | Min. bending radius, once only | 10 x cable diameter |
| Min. bending radius, repetitive | 20 x cable diameter | Resistance to spread of flame  | IEC 60754-2         |

## Plug

|           |                                                                    |            |                                                                    |
|-----------|--------------------------------------------------------------------|------------|--------------------------------------------------------------------|
| Plug left | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded | Plug right | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|--------------------------------------------------------------------|------------|--------------------------------------------------------------------|

## Plug, left

|           |                                                                    |
|-----------|--------------------------------------------------------------------|
| Plug left | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|--------------------------------------------------------------------|

## Plug, right

|            |                                                                    |
|------------|--------------------------------------------------------------------|
| Plug right | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded |
|------------|--------------------------------------------------------------------|

Creation date June 13, 2025 5:41:44 AM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

**IE-FM5Z2LM0050LD0LD0-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002607    | ETIM 7.0    | EC002607    |
| ETIM 8.0    | EC002607    | ETIM 9.0    | EC002607    |
| ETIM 10.0   | EC002607    | ECLASS 9.0  | 27-06-10-03 |
| ECLASS 9.1  | 27-06-10-03 | ECLASS 10.0 | 27-06-10-03 |
| ECLASS 11.0 | 27-06-10-03 | ECLASS 12.0 | 27-06-10-03 |
| ECLASS 13.0 | 27-06-10-03 | ECLASS 14.0 | 27-06-10-03 |
| ECLASS 15.0 | 27-06-10-03 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**


|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

**IE-FM5Z2LM0050LD0LD0-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**IE-FM5Z2LM0050LD0LD0-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****V0 material**

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

**Advantages:**

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

|            |                            |                                                                  |
|------------|----------------------------|------------------------------------------------------------------|
| Type       | VT SF 6/21 MC NE WS V0     | Version                                                          |
| Order No.  | <a href="#">1730560001</a> | SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm, |
| GTIN (EAN) | 4008190954611              | white                                                            |
| Qty.       | 160 pc(s).                 |                                                                  |
| Type       | VT SF 5/21 MC NE WS V0     | Version                                                          |
| Order No.  | <a href="#">1689470001</a> | SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm, |
| GTIN (EAN) | 4008190872571              | white                                                            |
| Qty.       | 160 pc(s).                 |                                                                  |