

CL 222 TM

●TM11R-5L *-88(50)

CL No.	Part No.	Type	RoHS
222-2667-3-50	TM11R-5L-88 (50)	Standard	YES
222-2668-6-50	TM11R-5LF-88(50)	With ferrite core	





Diagram illustrating the dimensions for a standard jack. The PCB width is 12.4. The distance from the PCB edge to the ferrite core is 0.6 or more. The distance from the PCB edge to the ferrite core is 2.3 or more. The ferrite core is labeled "Ferrite core".

(In a standard jack, this space is empty)

EMI-proof quadruplet right angle dip type connectors

●TM11R-5L *-3232(50)

CL No.	Part No.	Type	RoHS
222-2720-4-50	TM11R-5L-3232(50)	Standard	YES
222-2722-0-50	TM11R-5LF-3232(50)	With ferrite core	

[illegible][illegible]

– 39 –

MODULAR CONNECTORS

CL 222 TM

EMI-PROTECTED JACKS

GENERAL

The EMI-protected modular connectors have been developed from the TM Series connectors, to resist noise. Designed to comply with the FCC (Federal Communications Commission) 68 Standard, they range from standard parts to EMI-protected parts.

Furthermore, they are highly operable and resistant to severe environmental conditions to ensure customer satisfaction with shielding performance.

FEATURES



- (1) Plug connectors have a single-body shell and clamp to ensure secure protection from EMI.
- (2) To prevent electrostatic problems, plug connectors are designed so that the metal shell can be covered with a plastic hood.
- (3) Jack connectors that allow the shielded parts to be connected first during mating to protect the circuits within the set.
- (4) Plug harnesses can be wired easily and securely with a special tool.
- (5) Eight-conductor plugs and jack connectors comply with the ISO 8877 Standard (ISDN interface connector).

MAIN APPLICATIONS


ISDN related equipment, HBS, mobile telephones, office automation equipment.

JACKS WITH LEAD WIRES


TM11R-88-35S-300




CL No.	Part No.	RoHS
222-4449-3	TM11R-88-35S-300M	YES



Reference mounting drawing



Standard color arrangement



Note : Standard finish color is gray.



MODULAR CONNECTORS

CL 222 TM


Right angle dip type connectors

●TM11R-5C-66

CL No.	Part No.	RoHS
222-2148-6-50	TM11R-5C-66 (50)	YES






Board mounting dimensional drawing (connector side)




●TM11R-5C-88

CL No.	Part No.	RoHS
222-1378-0-50	TM11R-5C-88 (50)	YES



Board mounting dimensional drawing (connector side)



Note : Cover standard color is black.




MODULAR CONNECTORS

CL 222 TM


Right angle dip type connectors (With a decorative panel)

●TM11R-5E1-88 (50)

CL No.	Part No.	RoHS
222-3820-4-50	TM11R-5E1-88 (50)	YES






Board mounting dimensional drawing (connector side)




Straight dip type connectors

●TM11R-3C-88 (50)

CL No.	Part No.	RoHS
222-2133-9-50	TM11R-3C-88 (50)	YES



Board mounting dimensional drawing (connector side)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hirose Electric:

[TM11R-5C-88\(50\)](#) [TM11R-3C-88\(50\)](#) [TM11R-5C-66\(50\)](#) [TM11R-5LF-88](#) [TM11R-5LF-88\(50\)](#) [TM11R-5L-3232](#)
[TM11R-5L-3232\(50\)](#) [TM11R-5LF-3232\(50\)](#) [TM11R-5C-62\(50\)](#) [TM11R-5M2-88-LP\(30\)](#) [TM11R-5M2-88\(01\)](#) [TM11R-5C-64\(50\)](#) [TM11R-5N2-88](#) [TM11R-5N2-88\(50\)](#) [TM11RX-5C-88\(50\)](#) [TM11RUX-7DANA-IB-1028](#) [TM11R-5M3-88-LP](#)
[TM11R-5M3-88](#) [TM11R-5M3-88\(10\)](#)