



Drinking Cup Liner and Lid tested for safety per the U.S. Public Law 110 - 314, Consumer Product Safety, Improvement Act of 2008, Title I, Section 108 & California proposition 65.

Test Method: CPSC-CH-C1001-09.3 (Composite Test)

Di-butyl phthalate <0.015%
Butyl-benzyl phthalate <0.015%
Di-(2-ethyl-hexyl) phthalate <0.015%
Di-n-octyl phthalate <0.015%
Di-iso-nonyl phthalate <0.015%
Di-iso-decyl phthalate <0.015%
Di-n-hexyl phthalate <0.015%

Independent test laboratory report available upon request.

Description

- Replacement for static generating foam and plastic cups or water bottles on the workstation
- ESD Protective -
 - Bottom covered with slip resistant conductive rubber
 - Low charging
 - Stainless steel portion grounded when picked up by a grounded operator or when placed on a grounded ESD worksurface
 1 second Charge decay ± 1,000 volts to ± 100 volts tested per IEC 61340-5-1-1998 Test method B2
 - Bottom and cylindrical cup portions Rs < 1 x 10⁹ ohms per ANSI/ESD STM11.13
- Thermal Insulated Drinking Cup Perfect for hot or cold drinks.
 Drinking liner and inner portion of lid are insulative plastic to ensure personnel safety
- Reusable
- 16 ounces (470 mL), 7.5 inches (19.5 cm) tall
- Double wall with Stainless Steel exterior
- Stainless Steel push-on lid with slide opening
- BPA & toxin free
- Made in China

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20-2008 section 2.4 Sources of Static Electricity]

35890 Thermal Insulated Drinking Cup, Stainless Steel, 16 oz. (470 mL)

Specifications and procedures subject to change without notice.

Thermal Insulated Drinking Cup, Stainless Steel, 16 oz. (470 mL)

MENDA

3651 WALNUT AVE., CHINO, CA 91710

PHONE: (909) 627-2453 WEBSITE: MendaPump.com DRAWING NUMBER 35890 DATE: January 2019

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Menda: 35890